

Molded Parts Specification Control Drawing

Part Number : 222K163-8
Description : Boot, 90°, With Lip

NOTES

- All dimensions are in $\frac{\text{inches}}{\text{millimeters}}$
- Dimensions appearing in table are as follows:
 - a - As Supplied
 - b - After Unrestricted Recovery
- Molding ports are optional. When -00 modification number is specified molding ports will be located as shown.
- If eyelet clip (000W212) is required with part then add CS-1858 to description (i.e. 202K121-3-0-CS-1858).





TABLE OF DIMENSIONS

PART NUMBER	H		J		P ±10% b	R ±10% b	S ±10% b	T ±10% b	U ±10% b	JO ±10% b	HW ±20% b	JW ±20% b	X ±20% b	Y ±20% b
	Min	Max	Min	Max										
	a	b	a	b										
222K163-8	1.69 [43,0]	1.11 [28,2]	.98 [25,0]	.39 [9,9]	2.17 [55,0]	1.77 [45,0]	1.18 [30,0]	.12 [3,0]	.07 [1,7]	.63 [16,0]	.08 [2,0]	.04 [1,0]	.98 [25,0]	1.18 [30,0]

**If this document is printed it becomes uncontrolled.
Check for the latest revision.**



TYCO ELECTRONICS
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : B
Date : 3/03/03

Part Number : 222K163-8
Description : Boot, 90°, With Lip

Molded Parts Specification Control Drawing

Part Number : 222K163-8
Description : Boot, 90°, With Lip

COMPATABILITY CHART

MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-8	Polyolefin, Space	RT-1308	N/A		

ORDERING INFORMATION

222K163 -8 -XX /XX

Base part number _____

Material dash number _____
(See Compatibility Chart)

Modification number _____
(If necessary, see front of scd binder
for a complete list)

Adhesive slash number _____
(If necessary, see Compatibility Chart)

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR
NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION



TYCO ELECTRONICS
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : B
Date : 3/03/03

Part Number : 222K163-8
Description : Boot, 90°, With lip