



LOC	DIST	REVISIONS					
F	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			J	REACTIVATED	04JAN2005	JJD	YP



SEE INSTRUCTION SHEET 408-2028-2

Voir feuille d'instruction 408-2028-2



RECOMMENDED STRIP LENGTHS
(NOT TO SCALE)

220015-1	RG-225/U	AMP 225093-7	331987	1-51704-0	225082-1	225093-7
CRIMP TOOL	CABLE	MARKING	③ FERRULE QTY=1	② CONTACT QTY=1	① JACK ASS'Y QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN J.J. DESPREZ CHK T. CORRIOL APVD Y. PETRONIN 04JAN2005 04JAN2005 04JAN2005	tyco Electronics TYCO ELECTRONICS France SAS BP 30039, 95301 CERGY-PONTOISE Cedex			
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.41 3 PLC ± 4 PLC ± ANGLES ±3 FINISH		NAME JACK, WEATHERPROOF SERIES N		
MATERIAL -		APPLICATION SPEC -		SIZE A2	CAGE CODE 00779	DRAWING NO 225093-7
		WEIGHT -		RESTRICTED TO -		
				SCALE 3:1	SHEET 1	OF 1
				REV J		