



FOR USE WITH:
RG-223/U, 142A/U & 142B/U



ASSEMBLED VIEW



STRIP LENGTH

* SUPPLIED BY DANIELS MFG. CORP.
2266 FRANKLIN ROAD
BLOOMFIELD HILLS, MICH. 48013

1	225592-2	SEAL	4
1	1-225560-3	FERRULE	3
1	225800-2	CONTACT	2
1	225797-1	SHELL ASS'Y	1
QTY.	PART NO OR IDENTIFYING NO	NOMENCLATURE OR DESCRIPTION	ITEM NO

CENTER CONTACT CRIMPING TOOL:	M 2252012-C1 SETTING NO 5 POSITIONER 4344 * (AMP EQUIV. 1-61966-6) SEE I.S. 2348	220066-2
FERRULE CRIMPING TOOL:	220066-1 or 220066-2 CRIMP B	
	<i>RG-223/U</i>	<i>RG-142A/U & 142B/U</i>

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± ANGLES ±	CONTRACT NO	AMP AMP INCORPORATED Harrisburg, Pa. 17105			
	DR <i>S. Michael</i> 8-25-81				
	CHK <i>W. B. W.</i> 8-26-81	NAME <i>ARINC COAXIAL SOCKET SIZE 7</i>			
	MATERIAL	APPD <i>[Signature]</i> 8/24/81	SIZE B	FSCM NO 00779	DRAWING NO 225796-2
FINISH	APPD <i>S. Michael</i> 8-26-81	DSGN APPD	SCALE <i>NTS</i>	WT. <i>.14 OZ</i>	SHEET
	OTHER APPD				