




Temperature [°C]	R(T)/R25	Resistance [Ohms]	dR/R [%]	Rmin [Ohms]	Rmax [Ohms]
-25	12.990	129900	4.39	124202	135598
-20	9.676	96761	4.22	92675	100848
-15	7.276	72765	4.07	69806	75723
-10	5.522	55218	3.92	53056	57380
-5	4.227	42268	3.77	40674	43861
0	3.262	32624	3.63	31440	33808
5	2.538	25381	3.49	24494	26268
10	1.990	19897	3.36	19227	20566
15	1.571	15711	3.24	15202	16220
20	1.249	12493	3.12	12103	12882
25	1.000	10000	3.00	9700	10300
30	0.806	8056	3.11	7805	8307
35	0.653	6530	3.22	6319	6740
40	0.532	5324	3.33	5147	5501
45	0.437	4365	3.43	4215	4515
50	0.360	3599	3.53	3472	3726
55	0.298	2982	3.63	2874	3091
60	0.248	2484	3.72	2391	2576
65	0.208	2079	3.81	1999	2158
70	0.175	1748	3.90	1679	1816
75	0.148	1476	3.99	1417	1535
80	0.125	1252	4.07	1201	1303
85	0.107	1066	4.15	1022	1110
90	0.091	912	4.23	873	950
95	0.078	782	4.31	749	816
100	0.067	674	4.38	645	704
105	0.058	583	4.46	557	609

R ₂₅ (Ohms)	T _n Nominal T° (°C)	R _n (Ohms)	R _n tol.	B _{25/85}
10000	25	10000	3%	3984K

A1

0-2282093-1	A	NTC, WITH CABLE
TE PN	REV	DESCRIPTION

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT.
BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).

DIMENSIONS:
MASSE IN EINHEITEN:
(MM)

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
ALLGEMEINTOLERANZEN

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES/WINKEL ±°
FINISH/OBERFLÄCHE/FARBE

MATERIAL

-
-

DWN 05FEB2014
Maithreya K.P.
CHK 05FEB2014
Vishwa. A
APVD 06FEB2014
D. Weyrauch

PRODUCT SPEC
PRODUKTSPEZ.
-

APPLICATION SPEC
VERARBEITUNGSSPEZ.
-

WEIGHT
GEWICHT
2.4g

CUSTOMER DRAWING

/KUNDENZEICHNUNG

SCALE
MASSSTAB
4:1

SHEET
BLATT
1 OF 1

REV
A1

TE Connectivity

NAME
NTC, WITH CABLE
-

SIZE
A2

CAGE CODE
-

DRAWING NO.
ZEICHNUNGS-NR.
C=2282093

RESTRICTED TO
NUR FÜR
-

1471-9 (3/13)