




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	13JAN2021	RKL	DAO

- NOTES
- NV

NOTE NOT VALID
- 1

TOOL CAVITY MARKING
- 2

MATERIAL MARKING
- NV

-
- 4



PACKAGING: BULK MATERIAL IN CARDBOARD BOX
- 5

APPLICABLE FOR CONTACTCHAMBER DIAMETER OF Ø14MM
- 6

APPLICABLE FOR WIRE TYPE ACC. ISO 6722, THIN WALL
CABLE OUTER DIAMETER NEEDS TO BE CHECKED ACC. ISO 6722 TO SELECT CORRECT SWS
- 7

FOR ADDITIONAL INFORMATION SEE APPLICATION- SPEC
- 8

SEALING CLASS 3 (S3) QUALIFIED WITH CABLE ACW0219 (T4 ISO 6722-CLASS D)
WIRE SIZE 8mm² NOT QUALIFIED IN S3, AS NOT AVAILABLE IN T4 ISO 6722/CLASS D



ONLY FOR INFORMATION (ACC. ISO 6722 - THIN WALL)			
VARIANT	-3	-4	-5
DGB (mm²)	16	4-6	8-10
ISO-Ø (mm)	6.4-7.2	3.4-4.3	4.6-6.0
A	6.1	3.1	4.3

S3 8			S2			SEALING CLASS			
-	-	I	-	-	-	Insert 16mm ² (S3)	PBT	VIOLET	9
I	-	-	-	-	-	Insert 8-10mm ² (S3)	PBT	BLACK	8
-	I	-	-	-	-	Insert 4-6mm ² (S3)	PBT	GREEN	7
-	-	I	-	-	I	Sealing 16mm ²	VMO	GREEN	6
I	-	-	I	-	-	Sealing 8-10mm ²	VMO	BLUE	5
-	I	-	-	I	-	Sealing 4-6mm ²	VMO	GREY	4
-	-	-	-	-	I	Insert 16mm ²	PBT	VIOLET	3
-	-	-	I	-	-	Insert 8-10mm ²	PBT	BLACK	2
-	-	-	-	I	-	Insert 4-6mm ²	PBT	GREEN	1
1-2287390-5	1-2287390-4	1-2287390-3	2287390-5	2287390-4	2287390-3	DESCRIPTION	MATERIAL	COLOUR	ITEM NO.
2.25	2.44	1.98	1.88	1.35	1.76	WEIGHT OF EACH ASSY NO [g]			
PARTS LIST									

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±°
FINISH -
-

DWN R.K.LEME 04DEC2020

CHK D.A.OLIVEIRA 04DEC2020

APVD R.K.LEME 04DEC2020

PRODUCT SPEC 108-37122

APPLICATION SPEC 114-37033

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME SEALING WITH INSERT

SIZE A2

CAGE CODE 00779

DRAWING NO C-2287390

RESTRICTED TO

SCALE 5:1

SHEET 1 OF 1

REV A