



REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
	B	REV PER ECO 16-004866	4-14-16	CT	DM




RECEPTACLE SHELL
NICKEL PLATED
ALUMINUM ALLOY

4-40 JACKSCREW
STAINLESS STEEL,
3/32 HEX SOCKET HEAD
2X

.296

3



1



1 CONNECTOR KIT INCLUDES QUADRAX CONTACTS (TE PART# 1445692-3, QTY 2) FOR 100Ω CABLE.
SHOWN INSTALLED FOR REFERENCE ONLY.

2. RECOMMENDED CABLES :
RAYCHEM, CEC-RWC-18687, CEC-RWC-18664
TENSOLITE, NF24Q100, NF26Q100.

3 CONNECTOR IS MARKED WITH TE PART NUMBER, TE, CAGE CODE & DATE CODE.

4. OPERATING TEMPERATURE RANGE: -65°C TO 125°C (-85°F TO 257°F).

5. SILVER PLATED, STAINLESS STEEL RETENTION CLIPS ARE INSTALLED IN THE CONNECTOR.



---	2293403-2
	2293403-1
REMARKS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. GLATFELTER 04JUN2015	TE Connectivity	
		CHK D. MILLER 04JUN2015		
DIMENSIONS: IN		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME RECEPTACLE ASSY, LOW PROFILE RECTANGULAR QUADRAX, 202, SIZE 2, CABLE KIT
		0 PLC ±.01 1 PLC ±.01 2 PLC ±.01 3 PLC ±.005 4 PLC ±.01 ANGLES ±1° FINISH	APPLICATION SPEC	
MATERIAL	-	WEIGHT	-	SIZE A 1
-	-	CUSTOMER DRAWING	-	CAGE CODE -
-	-	SCALE	3:1	DRAWING NO 2293403
-	-	SHEET	1	RESTRICTED TO -
-	-	OF	1	REV B