










NOTES

- 1** MATERIAL: PA66 UL94-V0 GWT750°C NF CTI 350V
- 2** POLARIZATION RIB GO THROUGH TO HINGE.
POSITION "a" OR "b", AT CAVITY NO...
- 3** LOCKING DEVICE FOR COVER AT CAVITY NO
- 4** MATING STOP BETWEEN CAVITY NO 1 AND 2
ALSO BETWEEN THE LAST ONE AND LAST BUT ONE CAVITY
- 5** KEYING RIB POSITION "c" OR POSITION "d"
AT CAVITY NO
- 6** LOCKING LATCH BETWEEN CAVITY NO
- 7** CONTACT CAVITY NO
- 8** AREA FOR TE LOGO
- 9** DIMENSION A AND DIMENSION B SEE TABLE
- 10** CAVITY MARKING
- 11** PRELIMINARY PART NUMBER
- 12** ALTERNATE LOCKING LATCH GEOMETRY
- 13** PRODUCT WITH HIGH RETENTION FORCE EXCLUDING NOTE 15/LOCKING LATCH STANDARD VERSION:
MORE SPACE FOR LATCH ENGAGEMENT ARE NEEDED IN COUNT PART SIDE.
RECOMMEND SPACE: 4.0mm Min.
- 14** MATERIAL: PA66 UL-94 V0 & GWPT 750°C NO FLAME ACCORDING TO IEC 60335-1
- 15** LOCKING LATCH STANDARD VERSION, SEE SHEET 2.
- 16** PART WITH LOW CLOSING FORCE OF TPA: MAX. 75N
- 17** SPECIAL VERSION WITH INTERNAL LOCKING LATCH



SCALE 2:1




POSITION OF KEYING RIB
AND THE LOCKING LATCH
OF THE HOUSING


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Shown Li 12Mar2016	TE Connectivity	
DIMENSIONS:		CHK Federico Lupo 20May2016		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD Riccardo Babone 20May2016	NAME STANDARD-TIMER HOUSING	
	0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±1° FINISH	PRODUCT SPEC	SIZE	CAGE CODE
MATERIAL	-	APPLICATION SPEC	DRAWING NO	RESTRICTED TO
	-	WEIGHT	A100779	REV B6
CUSTOMER DRAWING		SCALE 3:1	SHEET 1 OF 2	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

 SPECIAL LOCKING LATCH GEOMETRY (STANDARD VERSION)
FOR PN 2-2295787-3





Other dimensions please refer to sheet 1



 5-2295787-5	5	05-B	25		NATURE
2295787-5	5	05-B	25		
2295787-4	4	-	20		
  2-2295787-3	3	-	15		COLOUR
2295787-3	3	03-G	15		
PART NO.	POS.	RAST 5	DIM A	MATERIAL	

 ONLY FOR 7 POSITION PART





SCALE 2:1

Other dimensions please refer to sheet 1

 5-2295787-7	7	-	35		NATURE
1-2295787-7	7	-	35		
2295787-7	7	07-C	35		
PART NO.	POS.	RAST 5	DIM A	MATERIAL	COLOUR

 SPECIAL VERSION WITH INTERNAL LOCKING LATCH



1-2483736-5	5	-	25		NATURE
2483736-3	3	03-A	15		
PART NO.	POS.	RAST 5	DIM A	MATERIAL	COLOUR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Shawn Li CHK Federico Lupo APVD Riccardo Babone	12Mar2016 20May2016 20May2016	TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME STANDARD-TIMER HOUSING	
mm		0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±1° FINISH -		PRODUCT SPEC APPLICATION SPEC SIZE CAGE CODE DRAWING NO A100779C=2295787	
MATERIAL		WEIGHT		RESTRICTED TO	
		CUSTOMER DRAWING		SCALE 3:1 SHEET 2 OF 2 REV B6	