

5 PLUG OPTION

OPTION '1'
(31 POSITION)

OPTION '2'
(36 POSITION)

LEVER LOCKED POSITION
LEVER ROTATION ANGLE
(67° FROM LEVER PRE-LOCK POSITION)

DELIVERY CONDITION
(LEVER PRE-LOCK)

SCALE 1:1

SECTION A-A

(32.06)

(30.78)

6 KEYCODE

A10 A9 A7 A6 A5 A4 A3 A2 A1

TYPE	P/N	WIRE SIZE (mm2)	CRIMPING INFORMATION	CAVITY PLUG
MOS CB (Au plating)	0-968220-5 or 5-968220-5	0.3/0.5	SEE TE SPEC. 114-61024	
	5-968221-5 or 5-968221-5	0.5/075		
MOS CB (Sn plating)	0-968220-1 or 5-968220-1 or 2005119-1 or 2390121-1	0.3/0.5	SEE TE SPEC. 114-61024	936054-1 or 2109258-4
	0-968221-1 or 5-968220-1 or 2005120-1 or 2390130-1	0.5/075		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±
FINISH -

MATERIAL
SEE TABLE

FINISH -

DWN
YH KIM

CHK
DG JEONG

APVD
YJ YOUN

PRODUCT SPEC
108-61404

APPLICATION SPEC
411-61070

WEIGHT
-

CUSTOMER DRAWING

NAME
36P PLUG ASSY

SIZE
A2

CAGE CODE
-

DRAWING NO
C-2296316

RESTRICTED TO
-

SCALE
1:1

SHEET
1

OF
2

REV
C

NOTE

1. GENERAL TOLERANCE : ±0.5, ±5°

2. DELIVERY CONDITION

3. LEVER LOCKED CONDITION

4. APPLICABLE CONTACT : SEE TABLE

5. WARPAGE MAX 0.6

6. APPLICABLE COVER : 2312414-1

1471-9 (3/13)

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

NO	OPTION	TE P/N	KEYCODE	① MAIN PLUG HSG (MATERIAL : PBT-GF15)		② CONTACT CARRIER (MATERIAL : PA66-GF15)		③ RETAINER (MATERIAL : PA66-GF30)		④ SEAL COVER (MATERIAL : PBT-GF30)			⑤ LEVER HSG (MATERIAL : PBT-GF30)		⑥ INNER SEAL (MATERIAL : SILICONE)		⑦ FAMILY SEAL (MATERIAL : SILICONE)	
				COLOR	QTY	COLOR	QTY	COLOR	QTY	COLOR	QTY	TYPE	COLOR	QTY	COLOR	QTY	COLOR	QTY
1	1	0-2296316-1	FREE	BLACK	1	BLACK	1	NATURAL	1	BLACK	1	GENERIC 1	GRAY	1	RED	1	RED ORANGE	1
2	2	9-2296316-9	FREE	BASALT GRAY	1	GRAY	1	YELLOW	1	BASALT GRAY	1	GENERIC 2	GRAY	1	RED	1	RED ORANGE	1
3	1	0-2296316-2	A1A2	BEIGE	1	BLACK	1	NATURAL	1	SIGNAL GREEN	1	TYPE 7	GRAY	1	RED	1	RED ORANGE	1
4	1	0-2296316-3	A1A3	BLUE LILAC	1	BLACK	1	NATURAL	1	YELLOW ORANGE	1	TYPE 2	GRAY	1	RED	1	RED ORANGE	1
5	1	0-2296316-4	A1A8	COBALT BLUE	1	BLACK	1	NATURAL	1	HEATHER VIOLET	1	TYPE 8	GRAY	1	RED	1	RED ORANGE	1
6	1	0-2296316-5	A1A5	BROWN BEIGE	1	BLACK	1	NATURAL	1	WINE RED	1	TYPE 3	GRAY	1	RED	1	RED ORANGE	1
7	1	0-2296316-6	A1A6	CLARET VIOLET	1	BLACK	1	NATURAL	1	RASPBERRY RED	1	TYPE 4	GRAY	1	RED	1	RED ORANGE	1
8	1	0-2296316-7	A1A7	CLAY BROWN	1	BLACK	1	NATURAL	1	BLUE LILAC	1	TYPE 5	GRAY	1	RED	1	RED ORANGE	1
9	1	0-2296316-8	A1A8	COBALT BLUE	1	BLACK	1	NATURAL	1	TRAFFIC YELLOW	1	TYPE 1	GRAY	1	RED	1	RED ORANGE	1
10	1	0-2296316-9	A1A9	CURRY YELLOW	1	BLACK	1	NATURAL	1	SIGNAL BLUE	1	TYPE 6	GRAY	1	RED	1	RED ORANGE	1
11	1	1-2296316-1	A1A10	EMERALD GREEN	1	BLACK	1	NATURAL	1	LEAF GREEN	1	TYPE 9	GRAY	1	RED	1	RED ORANGE	1
12	1	1-2296316-2	A2A3	FIR GREEN	1	BLACK	1	NATURAL	1	WINE RED	1	TYPE 3	GRAY	1	RED	1	RED ORANGE	1
13	1	1-2296316-3	A2A4	GREEN BEIGE	1	BLACK	1	NATURAL	1	LIGHT PINK	1	TYPE 11	GRAY	1	RED	1	RED ORANGE	1
14	1	1-2296316-4	A1A2	BEIGE	1	BLACK	1	NATURAL	1	LIGHT IVORY	1	TYPE 10	GRAY	1	RED	1	RED ORANGE	1
15	1	1-2296316-5	A1A3	BLUE LILAC	1	BLACK	1	NATURAL	1	SIGNAL BLUE	1	TYPE 6	GRAY	1	RED	1	RED ORANGE	1
16	1	1-2296316-6	A2A9	LIGHT PINK	1	BLACK	1	NATURAL	1	LIGHT IVORY	1	TYPE 10	GRAY	1	RED	1	RED ORANGE	1
17	1	1-2296316-7	A5A9	ROSE	1	BLACK	1	NATURAL	1	LIGHT PINK	1	TYPE 11	GRAY	1	RED	1	RED ORANGE	1
18	1	1-2296316-8	A2A8	LIGHT IVORY	1	BLACK	1	NATURAL	1	BLACK	1	GENERIC 1	GRAY	1	RED	1	RED ORANGE	1
19	2	1-2296316-9	A2A10	MELON YELLOW	1	GRAY	1	YELLOW	1	BASALT GRAY	1	GENERIC 2	GRAY	1	RED	1	RED ORANGE	1
20	1	2-2296316-1	A3A4	MOSS GREEN	1	BLACK	1	NATURAL	1	BLACK	1	GENERIC 1	GRAY	1	RED	1	RED ORANGE	1
21	1	2-2296316-2	A3A5	NUT BROWN	1	BLACK	1	NATURAL	1	BLACK	1	GENERIC 1	GRAY	1	RED	1	RED ORANGE	1
22	2	2-2296316-3	A3A6	OCEAN BLUE	1	GRAY	1	YELLOW	1	BASALT GRAY	1	GENERIC 2	GRAY	1	RED	1	RED ORANGE	1
23	2	2-2296316-4	A3A7	RASPBERRY RED	1	GRAY	1	YELLOW	1	BASALT GRAY	1	GENERIC 2	GRAY	1	RED	1	RED ORANGE	1
24	2	2-2296316-5	A3A8	ORANGE BROWN	1	GRAY	1	YELLOW	1	BASALT GRAY	1	GENERIC 2	GRAY	1	RED	1	RED ORANGE	1

⑦ SEAL COVER TYPE

GENERIC 1

GENERIC 2

TYPE 1

TYPE 2

TYPE 3

TYPE 4

TYPE 5

TYPE 6

TYPE 7

TYPE 8

TYPE 9

TYPE 10

TYPE 11

TYPE 12

THIS DRAWING IS A CONTROLLED DOCUMENT

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.1

2 PLC ±0.01

3 PLC ±0.001

4 PLC ±0.0001

ANGLES ±

FINISH

DWN YH KIM

CHK DG JEONG

APVD YJ YOUN

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME 36P PLUG ASSY

SIZE A2

CAGE CODE

DRAWING NO C-2296316

RESTRICTED TO

SCALE 1:1

SHEET 2 OF 2

REV C

TE

TE Connectivity

1471-9 (3/13)