




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	10SEP2016	RS	ML
	A1	REVISED PER ECR-16-016988	03JAN2017	RK	PO
	A2	REVISED PER ECR-24-226249	11NOV2024	NT	MZ
	A3	TAPE WIDTH UPDATE FOR 2305908-3	02DEC2024	KA	NKT



1. HOUSING MATERIAL: THERMOPLASTIC, FLAME-RETARDANT PER UL 94 V-0
COLOR = CHARCOAL GRAY
2. CONTACT MATERIAL: COPPER ALLOY WITH TIN PLATE
3. PRODUCT CERTIFICATIONS:
UL, CSA: 300V (SEE TABLE FOR RATED CURRENT)
4. HAZARDOUS SUBSTANCE COMPLIANCE: RoHS, REACH
5. PACKAGING: TAPE AND REEL
REEL DIAMETER = 380mm
TAPE WIDTH = SEE TABLE
6. MATES WITH 2213934 SERIES, 2213935 SERIES, AND 2305909 SERIES



10A UL GROUP D CSA GROUPS D, E	88	62.0	60.4	12	1-2305908-2
		57.0	55.4	11	1-2305908-1
15A UL GROUP B CSA GROUP B	72	52.0	50.4	10	1-2305908-0
		47.0	45.4	9	2305908-9
	56	42.0	40.4	8	2305908-8
		37.0	35.4	7	2305908-7
	44	32.0	30.4	6	2305908-6
		27.0	25.4	5	2305908-5
		22.0	20.4	4	2305908-4
		17.0	15.4	3	2305908-3
		24	12.0	10.4	2
	RATED CURRENT	TAPE WIDTH "W" (mm)	LENGTH "L2" (mm)	LENGTH "L1" (mm)	NO. OF POLES

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN RAVL.S	10SEP2016	 TE Connectivity		
			CHK M.LUKSIC	10SEP2016			
DIMENSIONS: mm			APVD M.LUKSIC	10SEP2016	NAME TERMINAL BLOCK HEADER, RIGHT ANGLE, SMT, 5.0MM PITCH		
			PRODUCT SPEC -				
			APPLICATION SPEC -				
MATERIAL SEE NOTES -	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±0.2 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH -	WEIGHT -	SIZE A2		CAGE CODE -	DRAWING NO C-2305908	RESTRICTED TO -
CUSTOMER DRAWING					SCALE 5:1	SHEET 1 of 2	REV A3

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

COPYRIGHT copyright.dbye-

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

2 POLES: 2305908-2

3 POLES: 2305908-3

4 POLES: 2305908-4

5 POLES: 2305908-5

6 POLES: 2305908-6

7 POLES: 2305908-7

8 POLES: 2305908-8

9 POLES: 2305908-9

10 POLES: 1-2305908-0

11 POLES: 1-2305908-1

12 POLES: 1-2305908-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC±0.2

1 PLC±0.13

2 PLC±0.13

3 PLC±0.13

4 PLC±0.13

ANGLES±0.13

FINISH-

DWNRAVL.S10SEP2016

CHKM.LUKSIC10SEP2016

APVDM.LUKSIC10SEP2016

PRODUCT SPEC-

APPLICATION SPEC-

WEIGHT-

CUSTOMER DRAWING

NAME

TERMINAL BLOCK HEADER, RIGHT ANGLE, SMT, 5.0MM PITCH

SIZEA2

CAGE CODE-

DRAWING NO.C-2305908

RESTRICTED TO-

SCALE5:1

SHEET2 OF 2

REV A3

TE

TE Connectivity

1471-9 (3/13)