






VIEW K
5:1





5
(0.1)
TPA IN
PRE-LOCKED POSITION

SECTION B-B



MAX Ø14
RING GAUGE
Huellkreis


SCALE 2:1



2306498-9 CODING Z AS SHOWN


- ONLY THE GERMAN LANGUAGE SHALL BE BINDING
Massgebend ist der deutsche Text
- DETAILS OF DESIGN ARE LEFT TO TE CONNECTIVITY
Einzelheiten der Ausfuehrung bleiben TE CONNECTIVITY ueberlassen
- PACKAGING: BULK IN CARDBOARD BOX
Verpackung: Schuettgut in Karton
- TE ORDER NO. 2306498-X SEE TABLE
TE-Bestellnummer 2306498-X siehe Tabelle
- CONDITION AS SUPPLIED: TPA IN PRE LOCKED POSITION
Anlieferzustand: Sekundaersicherung in Vorraststellung
- MATCHING TO CONTACT TE NO. e.g. 2298490 AND 2298511
Passend zu Kontakt TE-Nr. z.B. 2298490 und 2298511
- TE ORDER NUMBER ACCORDING TABLE
TE-Bestellnummer nach Tabelle
- ALL NOT SPEC. INTERFACE DIMENSIONS ARE ACCORDING
INTERFACE DRAWING 208-18048
Alle nicht definierten Schnittstellenmasse entsprechend
Schnittstellenzeichnung 208-18048
- SUITABLE MATING CONNECTOR TE-PN X-2306868-X
Passender Anschlusstecker TE-PN X-2306868-X

EXPLODED VIEW
SCALE 2:1



CODINGS, PLUG SIDE, SIMILARITY AS VIEW 5:1
Kodierung, Steckseite, Darstellung der Kodierungen nur aehnlich

TOLERANCE
Toleranz
 ± 0.1 A B



2306498-9	A	1	Z	TPA	PA66-GF30	TRAFFIC PURPLE	1.36	2
	A	1		HOUSING	PA66-GF30	WATER BLUE		1
2306498-6	A	1	F	TPA	PA66-GF30	TRAFFIC PURPLE	1.36	2
	A	1		HOUSING	PA66-GF30	NUT BROWN		1
2306498-5	A	1	E	TPA	PA66-GF30	TRAFFIC PURPLE	1.36	2
	A	1		HOUSING	PA66-GF30	MAY GREEN		1
2306498-4	A	1	D	TPA	PA66-GF30	TRAFFIC PURPLE	1.36	2
	A	1		HOUSING	PA66-GF30	CLARET VIOLET		1
2306498-3	A	1	C	TPA	PA66-GF30	TRAFFIC PURPLE	1.36	2
	A	1		HOUSING	PA66-GF30	LIGHT BLUE		1
2306498-2	A	1	B	TPA	PA66-GF30	TRAFFIC PURPLE	1.36	2
	A	1		HOUSING	PA66-GF30	PURE WHITE		1
2306498-1	A	1	A	TPA	PA66-GF30	TRAFFIC PURPLE	1.36	2
	A	1		HOUSING	PA66-GF30	JET BLACK		1
TE ORDER NO.	REV.	QTY.	COD.	DESCRIPTION	MATERIAL	COLOUR	WEIGHT [g]	POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN R. Nelson 15MAY2019		 TE Connectivity			
DIMENSIONS:				CHK M. Schoedel 16MAY2019					
mm				APVD K. Schreutlinger 20MAY2019					
TOLERANCES UNLESS OTHERWISE SPECIFIED:				PRODUCT SPEC		NAME		2POS. MATE-AX. PIN HSG. ASSY. 180DEG	
0 PLC ±0.2				108-94709		-		2pol. MATE-AX. Stiftgeh.. Zsb. 180Grad	
1 PLC ±0.2				APPLICATION SPEC		SIZE		CAGE CODE	
2 PLC ±0.2				116-94468		DRAWING NO		RESTRICTED TO	
3 PLC ±0.2				WEIGHT		A1 00779		©=2306498	
4 PLC ±0.2				CUSTOMER DRAWING		SCALE		10:1	
ANGLES FINISH						SHEET		1 OF 1	
MATERIAL						REV		A1	
-									
-									