






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A1		ECN-22-186507	24NOV22	L.Y	E.J
A2		ECN-23-224805	02AUG2023	L.Y	E.J
A3		ECN-24-284155	11SEP2024	N.L	E.J
A4		ECN-25-315611	08APR2025	K.F.Y	E.J



A-A



NOTES

- 1
- THIS PART IS UL94 V0 VERSION AND RELATED HB VERSION REFER TO TE DRAWING 2141155
- 2
- PACKAGING: BULK PACKAGING IN PLASTIC BAG AND CORRUGATED SHIPPING BOX

2310488-1	2310488-2	2310488-3	1-2310488-1	2-2310488-2

2-2310488-2	11.4	35 UNSHIELDING	PA66-GF UL94 V0	PROTECTION COVER	(3.3)	ORANGE
1-2310488-1	13.6	50 UNSHIELDING	PA66-GF UL94 V0	PROTECTION COVER	(3.3)	ORANGE
2310488-3	12.6	25	PA66-GF UL94 V0	PROTECTION COVER	(3.3)	ORANGE
2310488-2	14.8	35	PA66-GF UL94 V0	PROTECTION COVER	(3.3)	ORANGE
2310488-1	16.2	50	PA66-GF UL94 V0	PROTECTION COVER	(3.3)	ORANGE
PART NO	DIM. A	FOR WIRE SIZE (mm2)	MATERIAL	DESCRIPTION	WEIGHT (g)	SURFACE COLOR

A4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.LI	12SEP2017	TE Connectivity		
		CHK E.JIANG	15SEP2017			
DIMENSIONS:		APVD I.YIN	18SEP2017	NAME PROTECTION COVER		
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE A1		
		0 PLC	±0.3	CAGE CODE		
		1 PLC	±	DRAWING NO		
		2 PLC	±	RESTRICTED TO		
		3 PLC	±	A1 00779		
		4 PLC	±	C=2310488		
MATERIAL		ANGLES	±°	SCALE		
SEE TABLE		FINISH	-	3:1		
		CUSTOMER DRAWING		SHEET 1 OF 1		
				REV A4		