










|    |             |        |                             |           |               |              |              |         |
|----|-------------|--------|-----------------------------|-----------|---------------|--------------|--------------|---------|
| A4 | 3-2311621-1 | A-D    | REEL:<br>380*100*44mm       | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 3       |
|    |             |        |                             | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 2       |
|    |             |        |                             | 1         | 8 WAY HOUSING | PA10T OR SPS | BLACK        | 1       |
| A4 | 2-2311621-1 | A-D    | TRAY:<br>DIM 326*200*24.7mm | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 3       |
|    |             |        |                             | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 2       |
|    |             |        |                             | 1         | 8 WAY HOUSING | PA10T OR SPS | BLACK        | 1       |
| 2  | 1-2311621-2 | A-D    | TRAY:<br>DIM 310*210*29mm   | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 3       |
|    |             |        |                             | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 2       |
|    |             |        |                             | 1         | 8 WAY HOUSING | PA10T OR SPS | BLACK        | 1       |
|    | 1-2311621-1 | A-D    | TRAY:<br>DIM 320*210*28mm   | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 3       |
|    |             |        |                             | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 2       |
|    |             |        |                             | 1         | 8 WAY HOUSING | PA10T OR SPS | BLACK        | 1       |
|    | 2311621-4   | B-D    | TRAY:<br>DIM 375*275*30mm   | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 3       |
|    |             |        |                             | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 2       |
|    |             |        |                             | 1         | 8 WAY HOUSING | PA10T OR SPS | BLUE         | 1       |
|    | 2311621-3   | A-C    | TRAY:<br>DIM 375*275*30mm   | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 3       |
|    |             |        |                             | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 2       |
|    |             |        |                             | 1         | 8 WAY HOUSING | PA10T OR SPS | GREEN        | 1       |
|    | 2311621-2   | B-C    | TRAY:<br>DIM 375*275*30mm   | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 3       |
|    |             |        |                             | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 2       |
|    |             |        |                             | 1         | 8 WAY HOUSING | PA10T OR SPS | BROWN        | 1       |
|    | 2311621-1   | A-D    | TRAY:<br>DIM 375*275*30mm   | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 3       |
|    |             |        |                             | 4         | 0.63 SQ PIN   | CuZn30       | Sn OVER Ni   | 2       |
|    |             |        |                             | 1         | 8 WAY HOUSING | PA10T OR SPS | BLACK        | 1       |
|    | TE P/N      | CODING | PACKAGE                     | QTY       | DESCRIPTION   | MATERIAL     | COLOR/FINISH | ITEM NO |
|    |             |        |                             | PART LIST |               |              |              |         |



- 1 PLASTIC MATERIAL: PA10T OR SPS  
SQ PIN MATERIAL: CuZn30  
PLATING SPEC: TIN OVER NICKEL
- 2 MATERIAL MARKING
- 3 PLASTIC HOUSING PRODUCTION MONTH CLOCK
- 4 TOOL CAVITY MARKING 1,2,3,4...
5. PRODUCT OPERATION TEMPERATURE RANGE:-40°C~105°C
- 6 TE SEMIFINISHED PART NUMBER
7. SUITABLE MATING CONNECTOR: 2322346
- 8 TE-LOGO
- 9 TE SEMIFINISHED PART REVISION
- 10 PRODUCT STABILIZATION FOR SOLDERING PROCESS
- 11 PRODUCT ASSEMBLY DATA INFORMATION

|                                                                                       |  |                                        |  |                  |  |                                                                                                       |  |
|---------------------------------------------------------------------------------------|--|----------------------------------------|--|------------------|--|-------------------------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN<br>K.WEI                           |  | 20FEB2017        |  |  TE Connectivity |  |
|                                                                                       |  | CHK<br>E. JIANG                        |  | 21JUL2017        |  |                                                                                                       |  |
| DIMENSIONS:                                                                           |  | TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | APVD<br>LYIN     |  | NAME                                                                                                  |  |
| mm                                                                                    |  |                                        |  | 26JUL2017        |  | 8 WAY MQS PIN HEADER                                                                                  |  |
|  |  | 0 PLC ±                                |  | PRODUCT SPEC     |  | SIZE                                                                                                  |  |
|                                                                                       |  | 1 PLC ±0.1                             |  | 108-101528       |  | CAGE CODE                                                                                             |  |
|                                                                                       |  | 2 PLC ±0.01                            |  | APPLICATION SPEC |  | DRAWING NO                                                                                            |  |
| 3 PLC ±0.004                                                                          |  | 4 PLC ±0.0001                          |  | 114-101065       |  | RESTRICTED TO                                                                                         |  |
| ANGLES ±                                                                              |  | FINISH                                 |  | WEIGHT           |  | A2 - C=2311621                                                                                        |  |
| MATERIAL                                                                              |  |                                        |  | -                |  | SCALE                                                                                                 |  |
|  |  |                                        |  |                  |  | SHEET 1 of 1                                                                                          |  |
|                                                                                       |  |                                        |  | CUSTOMER DRAWING |  | REV A4                                                                                                |  |