









NOTES

- 1 DELIVERY CONDITION: SPACER (TPA) IN PRE-LOCK POSITION. PROTECT PLATE IN PRE-LOCK POSITION
- 2 TE ASSEMBLY PN SEE TABLE
- 3 MATING PART TE PN 2317733 (HOUSING) / 2317718 (COVER)
- 4 ONLY FOR INFORMATION. CHECK LATEST REVISION OF THE SUPPLIER SPECIFICATION FOR TERMINAL PROPERTIES
- 5 CONNECTOR VALIDATED TO GMW3191
- 6 WARPAGE MAX. +/-0.5mm ALLOWED


APPLICABLE COMPONENTS BOX 4				
DESCRIPTION	PLATING /COLOUR	SUPPLIER	SUPPLIER PART NO. (WIRE SIZE)	TE APPL. SPEC. TE PROD. SPEC.
MCON 1.2 CB	TIN	TE	1718348-1 (0.25-0.35mm ²)	-
MCON 1.2 CB	TIN	TE	1718350-1 (0.5-0.75mm ²)	-
MCON 1.2 CB	TIN	TE	/	-
OCS 1.2	TIN	DELPHI	3310134100.75-1.0mm ²	CONTACT TERMINAL SUPPLIER FOR DETAILED INFORMATION
OCS 1.2	TIN	DELPHI	3310134211.25-1.5mm ²	
1.5 FEMALE TERMINAL	TIN	YAZAKI	7114-4100-02 (0.35-0.5mm ²)	
1.5 FEMALE TERMINAL	TIN	YAZAKI	7114-4101-02 (0.75-1.0mm ²)	
1.5 FEMALE TERMINAL	TIN	YAZAKI	7114-4104-02 (0.5-1.5mm ²)	
OCS 1.5	TIN	DELPHI	1396478910.35-0.5mm ²	
OCS 1.5	TIN	DELPHI	1396479010.75-1.0mm ²	
OCS 1.5	TIN	DELPHI	139647911.5-1.5mm ²	
OCS 1.5	TIN	DELPHI	1396479211.5-2.0mm ²	
2.8 FEMALE TERMINAL	TIN	YAZAKI	7114-4110-02 (0.35-0.6mm ²)	
2.8 FEMALE TERMINAL	TIN	YAZAKI	7114-4111-02 (0.75-1.2mm ²)	
2.8 FEMALE TERMINAL	TIN	YAZAKI	7114-4112-02 (1.5-3.0mm ²)	
OCS 2.8	TIN	DELPHI	1396478010.75-1.0mm ²	
OCS 2.8	TIN	DELPHI	139647811.25-1.5mm ²	
OCS 2.8	TIN	DELPHI	1396478212.0-2.5mm ²	
OCS 2.8	TIN	DELPHI	1396478312.5-3.0mm ²	

1-2317734-1	A	A	57.7	2318946-1		PROTECT PLATE	PA66-GF50	RED	3
				2318943-1		SPACER (TPA)	PBT-GF10	GREY	2
				1-2318942-1		MALE HOUSING	PBT-GF30	BLACK	1
9-2317734-1	A	A	58.8	2318946-1	1	PROTECT PLATE	PA66-GF50	RED	3
				2318943-1	1	SPACER (TPA)	PBT-GF10	GREY	2
				9-2318942-1	1	MALE HOUSING	PBT-GF30	BLACK	1
5-2317734-1	A	A	57.7	2318946-1	1	PROTECT PLATE	PA66-GF50	RED	3
				2318943-1	1	SPACER (TPA)	PBT-GF10	GREY	2
				5-2318942-1	1	MALE HOUSING	PBT-GF30	BLACK	1
2317734-2	A	B	57.7	2318946-1	1	PROTECT PLATE	PA66-GF50	RED	3
				2318943-1	1	SPACER (TPA)	PBT-GF10	GREY	2
				2318942-2	1	MALE HOUSING	PBT-GF30	BLACK	1
2317734-1	A	A	57.7	2318946-1	1	PROTECT PLATE	PA66-GF50	RED	3
				2318943-1	1	SPACER (TPA)	PBT-GF10	GREY	2
				2318942-1	1	MALE HOUSING	PBT-GF30	BLACK	1
TE-ASSY-NO.	REV.	CODE	WEIGHT(g)	PART-NO	QTY	DESCRIPTION	MATERIAL	COLOUR	ITEM NO.




THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN J.ZONG 20JUL2017	STE TE Connectivity				
				CHK S.W.ANG 20JUL2017					
				APVD L.YIN 20JUL2017					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	NAME	92 WAY, TAB HSG			
		0 PLC ±1		108-101681	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		1 PLC ±0.5		APPLICATION SPEC					
		2 PLC ±0.2		116-101101					
		3 PLC ±0.1							
4 PLC ±0.1		ANGLES ±3°							
MATERIAL SEE TABLE		FINISH		WEIGHT		A1		00779 C=2317734	
				CUSTOMER DRAWING				SCALE 2:1 SHEET 1 OF 2 REV A2	

REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

0-2317734-1 AS SHOWN



1-2317734-1 AS SHOWN



1-2317734-1 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
J. ZONG
20JUL2017

CHK
S. W. ANG
20JUL2017

APVD
I. YIN
20JUL2017

NAME
92 WAY, TAB HSG
MCON 1.2CB, YA 1.5, YA 2.8
OCS 1.2, 1.5, 2.8

SIZE
A1

CAGE CODE
00779

DRAWING NO
©=2317734

RESTRICTED TO

TE Connectivity

PRODUCT SPEC
108-101681

APPLICATION SPEC
116-101101

WEIGHT
-

CUSTOMER DRAWING

SCALE
2:1

SHEET
2

OF
2

REV
A2

DIMENSIONS:
mm

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC

±1
±0.5
±0.2
±0.1
±0.1

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

±1°

MATERIAL
SEE TABLE
-

FINISH
-

ANGLES

±1°

4805 (3/13)