





D


C

B


A




- ⚠ MATERIAL: PA66, UL94V-0, COLOR: NATURAL
2. APPLICABLE CONTACT P/N  
2321928-1 OR 1-2321928-1
3. MATING CONNECTOR P/N  
PLUG HSG: 2321918-  
TPA (OPTIONAL): 2321927-  
GANG SEAL: 2321922- OR 2443732-\*
- 4 COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30(GWT)
- ⚠ PRELIMINARY PART - NOT RELEASED FOR PRODUCTION  
THIS PART HAS NOT COMPLETED QUALIFICATION TESTING
6. RECOMMENDED PANEL THICKNESS: 0.8 to 1.6mm.




1:2 POSITION




1:6 POSITION




1:3 POSITION




1:7 POSITION



1:4 POSITION



1:8 POSITION



1:5 POSITION

C

B

A

|         |         |         |         |         |         |      |             |
|---------|---------|---------|---------|---------|---------|------|-------------|
| 27.4    | 17.50   | 1.25    | 29.98   | 22.90   | 22.40   | 1*8  | ⚠ 2321926-8 |
| 24.9    | 15.00   | 0       | 27.48   | 20.40   | 19.90   | 1*7  | ⚠ 2321926-7 |
| 22.4    | 12.50   | 1.25    | 24.98   | 17.90   | 17.40   | 1*6  | 2321926-6   |
| 19.9    | 10.00   | 0       | 22.48   | 15.40   | 14.90   | 1*5  | 2321926-5   |
| 17.4    | 7.50    | 1.25    | 19.98   | 12.90   | 12.40   | 1*4  | 2321926-4   |
| 14.9    | 5.00    | 0       | 17.48   | 10.40   | 9.90    | 1*3  | 2321926-3   |
| 12.4    | 2.50    | 1.25    | 14.98   | 7.90    | 7.40    | 1*2  | 2321926-2   |
| DIM "F" | DIM "E" | DIM "D" | DIM "C" | DIM "B" | DIM "A" | POSN | PART NUMBER |

|                                        |  |                            |                           |              |
|----------------------------------------|--|----------------------------|---------------------------|--------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN B. WEAVER 15FEB2019    | TE Connectivity           |              |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | CHK S. FERNANDES 15FEB2019 |                           |              |
| DIMENSIONS: mm                         |  | APVD C. YI 15FEB2019       | NAME SDL 25 Panel         |              |
|                                        |  | 0 PLC ±                    | PRODUCT SPEC              |              |
|                                        |  | 1 PLC ±0.25                | 108-143069                |              |
|                                        |  | 2 PLC ±                    | APPLICATION SPEC          |              |
|                                        |  | 3 PLC ±                    | 114-143067                |              |
| MATERIAL                               |  | WEIGHT                     | SIZE CAGE CODE DRAWING NO |              |
| 1                                      |  | -                          | A1 00779 C=2321926        |              |
| CUSTOMER DRAWING                       |  | SCALE 3:1                  |                           | SHEET 1 OF 1 |
|                                        |  | REV A1                     |                           |              |