

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	08AUG2019	L.C	D.Z
	A1	ADD PART NUMBER	26MAY2021	L.C	D.Z
	A2	ADD PART NUMBER	29OCT2024	AR	CO

D

0.50 MAX
CUT-OFF

DIM A REF

DIM B

- 1

BRASS,0.20 THK, REF
- 2

FINISH: TIN PRE-PLATED
- 3


TE CONNECTIVITY LOGO LOCATED APPROX AS SHOWN
- 4

TO BE SUPPLIED WITH LOOSE
PIECE, SEE CUT-OFF DETIAL
- 5

MATING RECEPTACLE HOUSING P/Ns: 2321924-* OR 2321926-*
- 6


APPLICATION FEED 6.0mm

C





0.50 MAX
CUT-OFF

4 CUT-OFF DETAIL



B




PRE-PLATED CONTACT

LEAN VERSION	12.18	14.78	1.30-1.60	22-26 AWG	ON REEL	2	2321928-3
	12.78	15.38	1.30-1.60	22-26 AWG	LOOSE PIECE, SEE 4	2	1-2321928-1
	12.18	14.78	1.30-1.60	22-26 AWG	ON REEL	2	2321928-2
	12.78	15.38	1.30-1.60	22-26 AWG	ON REEL	2	2321928-1
REMARK	DIM B	DIM A	INSULATION DIA	WIRE RANGE	REMARKS	FINISH	PART NO

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.50
2 PLC ±0.25
3 PLC ±-
4 PLC ±-
ANGLES ±-

FINISH

SEE NOTES

DWN R.SMITH 28JUL2017

CHK C.YI 28JUL2017

APVD C.YI 28JUL2017

PRODUCT SPEC
108-143069

APPLICATION SPEC
114-143067

WEIGHT -

CUSTOMER DRAWING

STE TE Connectivity

NAME
TAB TERMINAL,
SDL 2.5 WATERPROOF
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2321928	-

SCALE	SHEET	OF	REV
5:1	1	1	A2