

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	08AUG2019	L.C	D.Z
	A1	ADD PART NUMBER	26MAY2021	L.C	D.Z
	A2	ADD PART NUMBER	29OCT2024	AR	CO
	B	MATERIAL TEMPER UPDATE	13JUN2025	AR	OC

0.50 MAX
CUT-OFF

DIM A REF

DIM B

- 1

BRASS,0.20 THK, REF
- 2

FINISH: TIN PRE-PLATED
- 3

TE CONNECTIVITY LOGO LOCATED APPROX AS SHOWN
- 4

TO BE SUPPLIED WITH LOOSE
PIECE, SEE CUT-OFF DETIAL
- 5

MATING RECEPTACLE HOUSING P/Ns: 2321924-* OR 2321926-*
- 6

APPLICATION FEED 6.0mm

0.50 MAX
CUT-OFF

4 CUT-OFF DETAIL

2.2±0.5

2.43
REF

SECTION T - T

1.8±0.5


1.49
REF

SECTION Y - Y

LEAN VERSION	12.18	14.78	1.30-1.60	22-26 AWG	ON REEL	2	2321928-3
	12.78	15.38	1.30-1.60	22-26 AWG	LOOSE PIECE, SEE 4	2	1-2321928-1
	12.18	14.78	1.30-1.60	22-26 AWG	ON REEL	2	2321928-2
	12.78	15.38	1.30-1.60	22-26 AWG	ON REEL	2	2321928-1
REMARK	DIM B	DIM A	INSULATION DIA	WIRE RANGE	REMARKS	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

1

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±0.50
2 PLC	±0.25
3 PLC	±-
4 PLC	±-
ANGLES	±-

FINISH

SEE NOTES

DWN
R.SMITH 28JUL2017

CHK
C.YI 28JUL2017

APVD
C.YI 28JUL2017

PRODUCT SPEC
108-143069

APPLICATION SPEC
114-143067

WEIGHT
-

CUSTOMER DRAWING

STE

TE Connectivity

NAME
TAB TERMINAL,
SDL 2.5 WATERPROOF
-

SIZE

A300779

CAGE CODE

C-2321928

DRAWING NO

SCALE
5:1

SHEET
1 OF 1

REV
B

PRE-PLATED CONTACT