

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	08AUG2019	L.C	D.Z
	A1	ADD PART NUMBER	26MAY2021	L.C	D.Z

0.50 MAX
CUT-OFF

DIM A REF

DIM B

1 BRASS, 0.20 THK, REF

2 FINISH: TIN PRE-PLATED

3 TE CONNECTIVITY LOGO LOCATED APPROX AS SHOWN

4 TO BE SUPPLIED WITH LOOSE PIECE, SEE CUT-OFF DETAIL

5 MATING RECEPTACLE HOUSING P/Ns: 2321924-* OR 2321926-*

6 APPLICATION FEED 6.0mm

4 CUT-OFF DETAIL

SECTION T-T

SECTION Y-Y

PRE-PLATED CONTACT

12.78	15.38	1.30-1.60	22-26 AWG	LOOSE PIECE, SEE 4	2	1-2321928-1
12.18	14.78	1.30-1.60	22-26 AWG	ON REEL	2	2321928-2
12.78	15.38	1.30-1.60	22-26 AWG	ON REEL	2	2321928-1
DIM B	DIM A	INSULATION DIA	WIRE RANGE	REMARKS	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN R. SMITH 28JUL2017

CHK C. YI 28JUL2017

APVD C. YI 28JUL2017

PRODUCT SPEC 108-143069

APPLICATION SPEC 114-143067

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME
TAB TERMINAL,
SDL 2.5 WATERPROOF

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2321928	-

SCALE	SHEET	OF	REV
5:1	1	1	A1

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±0.50
2 PLC	±0.25
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL

1

SEE NOTES

1470-19 (3/13)