


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED TO PRODUCTION STATUS	14JAN2021	EDB	EDB
	A1	ADDED -3 INFORMATION IN VIEW NOTES	30MAR2021	AJ	SZ
	B	ADDED DIM (C0.2*0.4) AND (4.55) IN 1C2	18MAY2022	AJ	SZ
	B1	REVISED PER ECN-25-324582	22JAN2025	SSH	JJ




- 1

HOUSINGS AND CONTACT OVERMOLDS: LCP, BLACK, UL94-V0.
CONTACTS: COPPER ALLOY.
SOLDER WASHERS: NICKEL SILVER.
- 2

0.76µm GOLD PLATING ON MATING INTERFACE. TIN
PLATE ON SOLDER TAILS. ALL OVER NICKEL UNDERPLATE
ON ENTIRE CONTACT.
- 3

MINIMUM PC BOARD THICKNESS:
SINGLE SIDED: 1.57 MIN
DOUBLE SIDED: 2.20 MIN
- 4

DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.

		WITH SOLDER WASHERS		2325864-3	
		WITH SOLDER WASHERS		2325864-2	
		AS SHOWN		2325864-1	
		DESCRIPTION		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SHIRK 02AUG2018		TE Connectivity RECEPTACLE CONNECTOR, 40 POSITION, SFP DD	
		CHK E. BRIANT 02AUG2018			
		APVD -			
		PRODUCT SPEC 108-130026			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ±		APPLICATION SPEC	
		1 PLC ±		114-130012	
		2 PLC ±		WEIGHT	
		3 PLC ±		-	
4 PLC ±		APPLICATION SPEC		SIZE	
ANGLES ±		114-130012		CAGE CODE	
MATERIAL		FINISH		DRAWING NO	
				RESTRICTED TO	
		CUSTOMER DRAWING		-	
				SCALE 5:1 SHEET 1 OF 3 REV B1	

