








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECR-18-017862	22NOV2018	SR	DD
	B	REVISED PER ECR-19-008311	06JUN2019	SR	DD
	B1	REVISED PER ECR-19-015297	01OCT2019	SB	DD
	B2	REVISED PER ECR-20-009266	09JUL2020	SB	DD

- 1

MATERIAL:
-POLYCARBONATE COLOR: SEE TABLE
2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
3. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING
4. MODULE BASE TE P/N: 2213837-1
5. PACKAGED 66 PER PLASTIC TRAY
DIM X = 24.25 - 7 TRAYS PER BOX
DIM X = 39.25 - 4 TRAYS PER BOX



2329013-1 AND 1-2329013-1
SHOWN
SCALE 2:1



2329013-2 AND 1-2329013-2
SHOWN
SCALE 2:1

26%	TRANSLUCENT GRAY	39.25	2-2329013-2
26%	TRANSLUCENT GRAY	24.25	2-2329013-1
78%	TRANSPARENT CLEAR	39.25	1-2329013-2
78%	TRANSPARENT CLEAR	24.25	1-2329013-1
24%	TRANSPARENT SMOKE	39.25	2329013-2
24%	TRANSPARENT SMOKE	24.25	2329013-1
APPROX. LIGHT TRANSMISSION	COLOR	DIM X	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. DAILY 10JAN2018	TE Connectivity	
		CHK M. STOLLER 10JAN2018		
DIMENSIONS: mm		APVD -	NAME DOME, LUMAWISE ENDURANCE S, 40mm	
		PRODUCT SPEC 108-133073	SIZE A200779	
		APPLICATION SPEC 114-133074		
		WEIGHT -	DRAWING NO C-2329013	
MATERIAL SEE TABLE		CUSTOMER DRAWING		RESTRICTED TO B2
		SCALE 5:2		SHEET 1 OF 1