

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20



(C) COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FIRST RELEASED	30MAY2018	J. J	W. H

PICK AND PLACE AREA
 $\varnothing 0.6$ RECOMMENDED P.C.B LAYOUT TOLERANCE ± 0.05

- PART NUMBER: 2336713-2.
- MATERIAL: SUS301 K1500, THICKNESS=0.08mm.
- FINISH : 2.0~7.6 μ m NICKEL UNDERLAYER ALL OVER.
0.25 μ m MIN. GOLD PLATING ON CONTACT AREA.
0.075~0.6 μ m GOLD PLATING ON SOLDER AREA.
- NORMAL FORCE: 0.5N MIN(INITIAL) AT WORKING RANGE.
0.4N MIN AFTER 1500CYCLES DURABILITY.
- WORKING RANGE: 0.80mm ~ 1.15 mm
- Δ Ni BARRIER AREA
- RATED CURRENT 1.5A, RATED VOLTAGE 10V DC.
- CONTACT RESISTANCE: 30 milliohm MAX INTIAL.
- OPERATION TEMPERATURE: -40~85 DEGREES.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± 0.1
1 PLC	± 0.1
2 PLC	± 0.01
3 PLC	± 0.001
4 PLC	± 0.0001
ANGLES	$\pm$
FINISH	-

DWN JONE JI 14MAY2018

CHK WENKE HF 14MAY2018

APVD WENKE HF 14MAY2018

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

SPRING FINGER 1.45H

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=2336713




SCALE 36:1

SHEET

1 OF 2

REV A

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD





WITH PRODUCT CHARGE
8000 EA/REEL
NO EMPTY POCKETS
ARE PERMITTED

160mm MIN
WITHOUT CHARGE

300mm MIN COVER TAPE
100mm MIN WITHOUT CHARGE

➔ DIRECTION OF TOP OF REEL



NOTE:
1. PACKAGE SPEC EIA-481-D

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 14MAY2018	 TE Connectivity	
		CHK WENKE HF 14MAY2018		
		APVD WENKE HF 14MAY2018		
		PRODUCT SPEC		
DIMENSIONS: mm		APPLICATION SPEC	NAME SPRING FINGER 1.45H	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± -		WEIGHT	SIZE A3	CAGE CODE 00779
0 PLC ±			DRAWING NO C=2336713	RESTRICTED TO
1 PLC ±0.1				
2 PLC ±0.01				
3 PLC ±0.001				
4 PLC ±0.0001				
ANGLES ±				
FINISH				
MATERIAL				
		CUSTOMER DRAWING	SCALE 36:1	SHEET 2 OF 2
				REV A