





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	22APR2019	BH	E.W
	A1	REVISED PER ECR-21-100734	23FEB2021	BH	E.W
	B1	REVISED PER ECR-23-193474	24NOV2023	BH	E.W
	B2	REVISED PER ECR-24-215915	06AUG2024	DB	RE




SECTION A - A
SCALE 8:1



SECTION B - B
SCALE 8:1

NOTES.
△ CUT-OFF LENGTH IS 0.5MM MAX.


YES	TIN-PLATING	24 - 20	Ø 1.0-Ø 1.8	BRASS 0.32+ THK	2339924-4
-	TIN-PLATING	24 - 20	Ø 1.0-Ø 1.8	BRASS 0.32+ THK	2339924-3
NO	TIN-PLATING	24 - 20	Ø 1.0-Ø 1.8	BRASS 0.32+ THK	2339924-2
NO	-	24 - 20	Ø 1.0-Ø 1.8	BRASS 0.32+ THK	2339924-1
LUBE	FINISH	WIRE SIZE	INSULATION SIZE	MATERIAL	PART NUMBER



2339924-1, -2



2339924-4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BH CHO	16JUL2018		 TE Connectivity		
		CHK -	-				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME .090 DIA PIN (2.3 DIA)			
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± ±0.4		PRODUCT SPEC 108-61421			
				APPLICATION SPEC 114-61250			
				WEIGHT -			
MATERIAL SEE TABLE		FINISH SEE TABLE		SIZE A3	CAGE CODE 00779	DRAWING NO C-2339924	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 5:1	SHEET 1	OF 1	REV B2