

THIS DRAWING IS UNPUBLISHED.




RELEASED FOR PUBLICATION

© COPYRIGHT — TE Connectivity Ltd.

ALL RIGHTS RESERVED.




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	THE OFFICIAL VERSION RELEASED	14MAY2019	R.Z	S.L




SPECIFICATION:

1. CURRENT RATING: 1.5A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. INSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES



A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME



15U"	2340901-3
30U"	2340901-2
G/F	2340901-1
GOLD PLATING THICKNESS	TEPN

6	SHELL	STAINLESS STEEL	NI Plated	1PCS
5	SHIELDING PLATE	STAINLESS STEEL	---	1PCS
4	MD	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
3	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
2	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ± —
	1 PLC ± 0.30
	2 PLC ± 0.20
	3 PLC ± 0.15
	4 PLC ± —
	ANGLES ± 3°
MATERIAL	FINISH
—	—

DWN	22JAN2019
CHK	22JAN2019
APVD	22JAN2019
PRODUCT SPEC	
APPLICATION SPEC	
WEIGHT	—

NAME			
USB TYPE C 2.0 CONN REC MID-MOUNT ONE ROW SMT TYPE WITH 0.035mm OFFSET			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2340901	—
CUSTOMER DRAWING		SCALE	SHEET
		1:1	1 OF 2
		REV	A

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT — TE Connectivity Ltd.





ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



SEE DETAIL X



	REEL	CARTON
CONNECTOR (PCS)	1500	15000

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 22JAN2019
RAMBO ZHANG
CHK 22JAN2019
RICHARD MA
APVD 22JAN2019
SIMON LI
PRODUCT SPEC

STE TE Connectivity

NAME
USB TYPE C 2.0 CONN REC MID-MOUNT
ONE ROW SMT TYPE WITH 0.035mm OFFSET

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH
MATERIAL —	—

WEIGHT —

CUSTOMER DRAWING

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2340901	—

SCALE 1:1 SHEET 2 OF 2 REV A