




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - TE Connectivity Ltd. ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A1	ECR-18-016210	12OCT2018	AW RB



RECOMEND BOARD PATTERN
 (NOT ACCUMULATE TOLERANCE)
 (CONNECTOR MOUNT SIDE)

- NOTES
- MATERIAL: HOUSING: GLASS FILED THERMO PLASTIC, UL 94V-0
 CONTACT: COPPER ALLOY
 RETENTION LEG: COPPER ALLOY
 - FINISH (CONTACT AREA): 0.38um MIN GOLD PLATING OVER NI PLATING
 - FINISH (RETENTION LEG): TIN PLATED OVER NICKEL (SOLDER TYING)

TAPE & REEL		1-2343327-2
PACKAGE	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ALVIN.WANG 31JUL2018	TE Connectivity Ltd.	
		CHK RICK.BIAN 31JUL2018		
DIMENSIONS: mm		APVD RICK.BIAN 31JUL2018	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	5 POS SINGLE ROW SMT TYPE	
0 PLC ± -		108-5349	HORIZONTAL HDR ASSY FOR DYNAMIC 3100	
1 PLC ± 0.4		APPLICATION SPEC	-	
2 PLC ± 0.3		114-5148	SIZE A3	CAGE CODE 00779
3 PLC ± -		WEIGHT -	DRAWING NO C=2343327	
4 PLC ± -		CUSTOMER DRAWING	RESTRICTED TO -	
ANGLES ± 3°			SCALE 2:1	SHEET 1 OF 2
MATERIAL SEE NOTE	FINISH SEE NOTE			REV A1

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-. - .

REVISIONS


© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-

UNWINDING DIRECTION →

1-2343327-2 PACKAGING



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ALVIN.WANG 31JUL2018	TE Connectivity Ltd.	
		CHK RICK.BIAN 31JUL2018		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD RICK.BIAN 31JUL2018	NAME 5 POS SINGLE ROW SMT TYPE HORIZONTAL HDR ASSY FOR DYNAMIC 3100	
	0 PLC ± - 1 PLC ± 0.4 2 PLC ± 0.3 3 PLC ± - 4 PLC ± - ANGLES ± 3'	PRODUCT SPEC 108-5349	RESTRICTED TO	
MATERIAL SEE NOTE	FINISH SEE NOTE	APPLICATION SPEC 114-5148	SIZE A3	CAGE CODE 00779
		WEIGHT -	DRAWING NO C=2343327	
		CUSTOMER DRAWING		SCALE 2:1
		SHEET 2 OF 2		REV A1