








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




DETAIL S(10:1)



DETAIL P(10:1)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CHK APVD		TE TE Connectivity Ltd.	
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0. PLC 1. PLC 2. PLC 3. PLC 4. PLC ANGLES		PRODUCT SPEC APPLICATION SPEC	
		± 0.3		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL		FINISH		WEIGHT A2 00779 C-2347090	
-		-		-	
CUSTOMER DRAWING				SCALE N.TS SHEET 2 of 6 REV A1	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



VIEW W

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES, UNLESS OTHERWISE SPECIFIED:

0. PLC $\pm$
1. PLC $\pm$
2. PLC $\pm$
3. PLC $\pm$
4. PLC $\pm$
ANGLES $\pm$

DWN
-
CHK
-
APVD
-

PRODUCT SPEC
-
APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

SCALE
NTS

TE Connectivity Ltd.

NAME
SOCKET E1 ASSY
LGA4677-1

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2347090

RESTRICTED TO
-

SHEET
3 OF 6

REV
A1

1471-9 (1/15)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

D

C

B


A

D


C

B


A




BALL SIDE BOARD LAND PATTERN



DETAIL Q (X6)



DETAIL P




DETAIL N(20:1)

DETAIL M(20:1)

KOZ LEGEND FOR REFERENCE:	
	ZONE 3: NO ROUTE ZONE,THOUGH ALL LAYERS
	ZONE 2: SOCKET CAVITY TO SOCKET ZONE. NO COMPONENT PLACEMENT ALLOWED 0.0mm HEIGHT RESTRICTION.
	ZONE 1: SOCKET CAVITY 1.222mm HEIGHT RESTRICTION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CHK APVD		 TE Connectivity Ltd.						
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME						
		0. PLC ±		SOCKET E1 ASSY LGA4677-1						
		1. PLC ±								
		2. PLC ±								
		3. PLC ±								
		4. PLC ±								
ANGLES ±		PRODUCT SPEC		SIZECAGE CODEDRAWING NORESTRICTED TO						
APPLICATION SPEC										
MATERIAL	FINISH	WEIGHT		A200779C=2347090						
		CUSTOMER DRAWING		SCALE		NTS	SHEET	5 of 6	REV	A1



SOCKET E1 HARD TRAY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN — CHK — APVD —		 TE Connectivity Ltd.	
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
		Q. PLC ± — 1. PLC ± — 2. PLC ± — 3. PLC ± — 4. PLC ± — ANGLES ± —		PRODUCT SPEC —	
		APPLICATION SPEC —		SIZE A2	
		WEIGHT —		CAGE CODE 00779	
MATERIAL —		FINISH —		DRAWING NO C=2347090	
CUSTOMER DRAWING				RESTRICTED TO —	
				SCALE NTS	
				SHEET 6 of 6	
				REV A1	