



© 2019 TE Connectivity. All Rights Reserved.	
PROJECT	PR-16-000909157
PART NO.	2358544-1,2358544-2
DESCRIPTION	D-SUB METAL LONG HOOD SIZE 1
CUSTOMER	GENERAL MARKET


REFER SHEET 2 FOR
PART NUMBERS TO BE ORDERED SEPERATELY

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	18JUN2019	GK	SE
	A1	-2 ADDED TO THE DRAWING	13MAY2020	GK	SE


NOTES:
1. TEMPERATURE RANGE: -40°C TO +90°C



SCALE 1:1






SCALE 1:1



M3

SECTION A - A



9	2	-	CYLINDER HEAD SCREW ISO4762 UNC4-40
8	-	2	CYLINDER HEAD SCREW ISO4762 M3X17.5-8.8
7	2	2	SPRING RING ZINC PLATED
6	1	1	BARREL ZINC PLATED
5	1	1	WASHER A3 SN PLATED
4	1	1	GROUNDING SCREW
3	4	4	SCREW FOR LID
2	1	1	D-SUB METAL HOOD 9 POSITION, LID
1	1	1	D-SUB METAL HOOD 9 POSITION, HOUSING
POSITION			-2 -1
QTY REQUIRED PER ASSEMBLY			PART DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 18JUN2019 GOPALAKRISHNA HV	TE Connectivity		
		CHK 18JUN2019 S EGBERT			
		APVD 18JUN2019 S EGBERT	NAME D-SUB METAL LONG HOOD SIZE 1		
		PRODUCT SPEC			
		APPLICATION SPEC			
		WEIGHT			
RESTRICTED CUSTOMER		SCALE 1:1		SHEET 1 OF 2	REV A1

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

PART NUMBERS TO BE ORDERED SEPERATELY

2308272
CABLE CLAMP




2308349
CRIMP FLANGE



2308350
CRIMP BARREL



2334099
2334100
CONNECTOR




2334110
2334108
CONTACT



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.0
1 PLC ±.0
2 PLC ±.0
3 PLC ±.0
4 PLC ±.0
ANGLES ±.0

MATERIAL

-

FINISH

-

DWN 18JUN2019

GOPALAKRISHNA HV

CHK 18JUN2019

S EGBERT

APVD 18JUN2019

S EGBERT

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

RESTRICTED CUSTOMER



TE Connectivity

NAME
D-SUB METAL LONG HOOD SIZE 1

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-2358544

SCALE 1:1

SHEET 2 OF 2

REV A1