




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ADD CAP	09NOV2021	AL	SH
	B	UPDATING CROWN BAND DESIGN	13NOV2024	MRM	WY
	C	UPDATING CAP AND TR VIEWS	17DEC2024	MRM	WY
	C2	ADD -2 OPTION	28FEB2025	MRM	WY




PICK AND PLACE CAP HIDDEN




SECTION A - A
SCALE 5:1



PICK AND PLACE CAP SHOWN



PICK AND PLACE CAP HIDDEN





RECOMMENDED PCB LAYOUT

1. MATERIAL:
HOUSING AND CONTACT: COPPER ALLOY
PICK AND PLACE CAP: LCP
2. FINISH:
ROUND SOCKET: 3um SILVER PLATING OVER 1.27um NICKEL PLATING
CROWN BAND CONTACT: 0.76um GOLD PLATING OVER 1.27um NICKEL PLATING
3. ELECTRICAL PERFORMANCE: 200 AMPS

NO CAP	2361371-2
CAP	2361371-1
COMMENT	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANDY LI	16AUG2019	TE Connectivity		
		CHK -	-			
DIMENSIONS: mm		APVD SUNY ZHAO	16AUG2019	NAME PIN SIZE 8mm, SOCKET ICCON INSERT		
		PRODUCT SPEC	108-128111	SIZE A2		
		APPLICATION SPEC	114-128112			
MATERIAL 		WEIGHT -	-	CAGE CODE 00779	DRAWING NO C-2361371	RESTRICTED TO -
		CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 2	REV C2

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET I			



PACKING SPECIFICATION FOR 2361371-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANDY LI	16AUG2019	TE Connectivity			
DIMENSIONS:		CHK -	-	NAME PIN SIZE 8mm, SOCKET ICCON INSERT			
mm		APVD SUNY ZHAO	16AUG2019				
		PRODUCT SPEC	108-128111	SIZE			
		APPLICATION SPEC	114-128112	CAGE CODE			
		MATERIAL	-	DRAWING NO			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT	-	A2		00779	
FINISH		CUSTOMER DRAWING		SCALE		4:1	
				SHEET		2 OF 2	
						REV	
						C2	