





© 2021 TE Connectivity. All Rights Reserved.

| REVISIONS |     |               |           |     |      |
|-----------|-----|---------------|-----------|-----|------|
| P         | LTR | DESCRIPTION   | DATE      | DWN | APVD |
|           | E   | ECR-23-184268 | 16AUG2023 | NR  | DJ   |
|           | E1  | ECR-23-187176 | 15SEP2023 | NR  | DJ   |
|           | E2  | ECR-23-192648 | 15NOV2023 | NR  | DJ   |
|           | E4  | ECR-24-200485 | 16FEB2024 | MI  | DJ   |



ISOMETRIC VIEWS  
SCALE 4:1



- 1 FRONT OUTER CONTACT: PHOSPHOR BRONZE.  
REAR OUTER CONTACT: COPPER ALLOY.  
DIELECTRIC: POLYESTER PBT, NATURAL.
- 2 FRONT & REAR OUTER CONTACTS: PREPLATED 1.0µm MIN TIN.
3. NOTE DELETED.
4. PACKAGED ON REEL.
5. DIE FEED = 19.5mm.
6. 2368036-1 AS SHOWN.

|                                                   |                |
|---------------------------------------------------|----------------|
| DACAR 585-3, DACAR 686-3,<br>G&G X9305, G&G X9534 | 2368036-1      |
| APPLICABLE<br>CABLE SIZE                          | PART<br>NUMBER |

|                                        |                                                                 |                                   |                                                                  |                    |                         |                    |
|----------------------------------------|-----------------------------------------------------------------|-----------------------------------|------------------------------------------------------------------|--------------------|-------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |                                                                 | DWN<br>D. J. HARDY<br>02FEB2021   | TE Connectivity                                                  |                    |                         |                    |
| DIMENSIONS:                            |                                                                 | CHK<br>N. W. SWANGER<br>03FEB2021 |                                                                  |                    |                         |                    |
| mm                                     | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:                       | APVD<br>J. W. HALL<br>03FEB2021   | NAME<br>OUTER CONTACT SUBASSEMBLY, FEMALE,<br>180 DEGREE, GEMNET |                    |                         |                    |
|                                        | 0 PLC ±<br>1 PLC ±<br>2 PLC ±<br>3 PLC ±<br>4 PLC ±<br>ANGLES ± | PRODUCT SPEC<br>-                 | SIZE<br>A2                                                       | CAGE CODE<br>00779 | DRAWING NO<br>C-2368036 | RESTRICTED TO<br>- |
|                                        | MATERIAL<br>-1                                                  | FINISH<br>-2                      | APPLICATION SPEC<br>114-32334                                    | WEIGHT<br>-        | SCALE<br>8:1            | SHEET<br>1 OF 1    |
| CUSTOMER DRAWING                       |                                                                 |                                   |                                                                  | REV<br>E4          |                         |                    |