






P		LTR		DESCRIPTION	DATE	DWN	APVD
A1		ECN-22-184653			15NOV22	L.D	J.Z
A2		ECN-23-193184			10JAN23	L.D	J.Z
A3		ECN-23-208643			18APR23	L.D	J.Z
A4		ECN-24-271452			19JUN2024	GSK	J.Z

COVER CLOSED PICTURED



OPENING GUIDE: TO OPEN THE LOCKED RETAINER, USE A Ø 1x0.18MM SCREWDRIVER AND PUSH IT IN THE SHOWN OPENING.

2368247-1 AS SHOWN



NOTES:

- 1 MATING PART EXECUTION ACC. 114-18161-001
- 2 SUITABLE CONTACTS 1355717, 928999, 963715
- 3 MATERIAL REMOVAL OPTIONAL IN EXECUTION AND
POSITION ACC. TO MANUFACTURER POSSIBLE
- 4 PACKAGING: LOOSE PIECE IN CARDBOX
5. CONDITION ON DELIVERY:
SECONDARY LOCK DEVICE SHOULD BE IN PRELOCK POSITION
--IF IN ENDOCK POSITION AFTER TRANSPORTATION,
PLEASE REOPEN IT IN ACCORDANCE THE OPENING GUIDE

2368247-8	A	D	PBT-GF10	BLACK	9011	1.52	8
2368247-6	A	B	PBT-GF10	GREEN	6018	1.54	5
2368247-4	A	D	PBT-GF10	BLUE	5012	1.53	4
2368247-3	A	C	PBT-GF10	RED	2002	1.53	3
2368247-2	A	B	PBT-GF10	BROWN	1011	1.54	2
2368247-1	A	A	PBT-GF10	BLACK	9011	1.52	1
TE PART NO.	REV.	COD.	MATERIAL	COLOUR	RAL	WEIGHT [g]	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DRAWN J.LEE 17/JAN/2020		 TE Connectivity			
DIMENSIONS: mm		CHECKED J.ZONG 17/JAN/2020					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROVED J.YIN 17/JAN/2020					
		PRODUCT SPEC		NAME 6POSN. MQS REC. HOUSING			
0 PLG ± 1 PLG ± 2 PLG ± 3 PLG ± 4 PLG ± ANGLES ±1°		APPLICATION SPEC		-			
MATERIAL	FINISH	WEIGHT	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-	-	CUSTOMER DRAWING		A	00779	G=2368247	
				SCALE	5:1	SHEET	1 of 1
				REV	A4		

TOLERANCES UNLESS OTHERWISE SPECIFIED ACC. TO DIN 16901-140 CENTRIC TO NOMINAL DIMENSION. EDITION 1982-11 SHALL APPLY.
Freiungstoleranzen nach DIN 16901-140. Es gilt die Ausgabe 1982-11.