




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	TRACEABILITY LABEL ADDED NOTE 15 ITEM 4	25AUG2022	RL	WY

2368252-1	-
TE P/N	CUSTOMER P/N,REV.

- NOTES:
- 100% ELECTRICAL TEST FOR CONTINUITY, OPENS AND SHORTS.
 - ROHS COMPLIANCE: PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE SPECIFICATION TEC-138-702.
 - LABEL TEXT AS BELOW.

2368252-X
YYWW
MADE IN ---

TE P/N
DATE CODE
COUNTRY OF ORIGIN

4. SERIALIZATION LABEL, PASTE ON THE CONNECTOR SURFACE AS SHOWN

XXXXXXX-X
LXXXXX
|||||||

TE P/N
LOCATION CODE L=("D" FOR DGN OR "A" FOR MEXICO), SERIES NUMBER
BARCODE READ AS TE P/N, LOCATION CODE AND SERIES NUMBER

WIRING CHART		
FROM	TO	COLOR
J1-P1	J2-P1	RED
J1-P4		
J1-P2	J2-P3	GRN/YEL
J1-P3	J2-P4	BLACK
J1-P6		
J1-P5	J2-P2	WHITE
J2-D2		WHITE

1	PC	LABEL, 9.525X17.78	15
1	PC	MBXLE SIGNAL TERMINAL	14
AR	MR	WIRE 22AWG WIHTE, UL1061	13
1	PC	LABEL	12
AR	MR	EXPAND BRAID SLEEVE, BLACK	11
AR	MR	H.S.T	10
2	PC	MBXLE CONTACT Au PLATED 10AWG	9
2	PC	MBXLE CONTACT Au PLATED 12AWG	8
1	PC	MBXLE 4P+16S+4P	7
AR	MR	WIRE 12AWG YELLOW/GREEN, PVC	6
AR	MR	WIRE 12AWG WHITE, PVC	5
AR	MR	WIRE 12AWG RED, PVC	4
AR	MR	WIRE 12AWG BLACK, PVC	3
6	PC	MEGA FIT CONTACT 15u" Au PLATED	2
1	PC	MEGA FIT 6P 5.7PITCH	1
QTY	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Kylin Yao	17JAN2020	TE Connectivity			
		CHK -	-				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME Cable Assy, MBXLE To Mega Fit			
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		APVD William Yao			
				PRODUCT SPEC			
MATERIAL -				APPLICATION SPEC			
				-			
				WEIGHT 0	SIZE A2	CAGE CODE 00779	DRAWING NO C-2368252
				CUSTOMER DRAWING			
				RESTRICTED TO -			
				SCALE N.T.S			
				SHEET 1 of 1			
				REV A			