



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	I	PRELIMINARY	09JUN2020	-	-
	A	RELEASED PER ECN-23-233926	11OCT2023	MM	DR

MT FERRULE KIT
(COMPONENTS PACKAGED UNASSEMBLED)
2375153-1 SHOWN



- 1 MATERIAL= MT FERRULE: THERMOPLASTIC PER ASTM D4067
FERRULE COVER: ABS PER ASTM D4673
MINI BOOT: VULCANIZED THERMOPLASTIC POLYOLEFIN
SPRING: 300 SERIES, STAINLESS STEEL WIRE, PER ASTM A313
PIN HOLDER: 300 SERIES, STAINLESS STEEL, PER ASTM A617
PINS: 400 SERIES, STAINLESS STEEL, PER ASTM A276
- 2 FINISH= SPRING: PASSIVATED

24 FIBER, MULTI-MODE, LOW-LOSS GRADE	2375153-2
12 FIBER, MULTI-MODE, LOW-LOSS GRADE	2375153-1
MT FERRULE TYPE	KIT PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CHK	D. FABIAN	09JUN2020	 TE Connectivity			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	KIT, MT FERRULE WITH PINS NEW UNIVERSALS			
mm		APVD	-	PRODUCT SPEC	APPLICATION SPEC			
		0 PLC ±		SIZE	CAGE CODE	DRAWING NO		
		1 PLC ±		A	00779	©=2375153		
		2 PLC ±0.13						
		3 PLC ±0.013						
4 PLC ±		WEIGHT	-	RESTRICTED TO	-			
ANGLES		FINISH		CUSTOMER DRAWING				
MATERIAL		1		2		SCALE 8:1	SHEET 1 OF 1	REV A