







REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECR-24-216443	31JUL24	C.X	L.C

- 1 MATERIAL: PBT, UL94V-0, COLOR: BLACK
2. RECOMMENDED MATING PART:[]-2379778-[],
3. PACKAGING: LOOSE PIECE





19.9	BLACK	7	7-2377775-1
17.4	BLACK	6	6-2377775-1
15.9	BLACK	5	5-2377775-1
12.4	BLACK	4	4-2377775-1
9.9	BLACK	3	3-2377775-1
DIM.A	COLOR	POS.	PART NO.


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. XU 9DEC2021		TE Connectivity									
DIMENSIONS: mm		CHK D. ZHANG 10DEC2021											
		APVD D. ZHANG 10DEC2021		NAME TPA , NEW G12.5 SERIES									
		PRODUCT SPEC 108-106077											
		APPLICATION SPEC 114-160215											
		WEIGHT -		SIZE A3		CAGE CODE 00779		DRAWING NO C-2377775		RESTRICTED TO -			
		MATERIAL 		FINISH -									
				CUSTOMER DRAWING				SCALE NA		SHEET 1 OF 2		REV B	

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET1			


3P





4P





5P




6P



7P



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. XU	9DEC 2021	TE Connectivity				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK D. ZHANG	10DEC 2021					
		APVD D. ZHANG	10DEC 2021	NAME TPA , NEW G12.5 SERIES				
		PRODUCT SPEC 108-106077						
	0 PLC ±	NAME TPA , NEW G12.5 SERIES						
	1 PLC ±0.20							
2 PLC ±								
3 PLC ±								
4 PLC ±								
MATERIAL 	ANGLES ±	APPLICATION SPEC 114-160215	SIZE A 3	CAGE CODE 00779	DRAWING NO C-2377775	RESTRICTED TO -		
	FINISH -	WEIGHT -	CUSTOMER DRAWING			SCALE NA	SHEET 2 OF 2	REV B