


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	27OCT2022	E.C	Z.Z



1. MATERIAL: PA66 GF-30  
 FLAMMABILITY: UL94 V-0  
 COLOR: SEE TABLE

2. FEATURE DENOTED BY REFERENCE DIMENSIONS MUST BE INSPECTION FOR PRESENCE

3. PART MUST BE FREE OF EXCESSIVE FLASH, MIS-MATCH, SINK MARKS. OR OTHER VISUAL IMPERFECTIONS THAT MAY AFFECT PRODUCT FIT OR FUNCTION

4. BULK PACKAGED

12.0	12.8	11.9	ORANGE	FOR 3X6SQM ISO H+S	2392558-4
10.6	11.4	10.6	NATURAL	FOR 2X6SQM ISO H+S	2392558-3
9.7	10.5	9.7	GRAY	FOR 2X4SQM ISO H+S FOR 3X4SQM ISO H+S	2392558-2
8.1	8.7	8.1	BLACK	FOR 2X2.5SQM ISO H+S FOR 3X2.5SQM ISO H+S	2392558-1
MIN.	MAX.	DIM. A	COLOR	DESCRIPTION	PART NO.
WIRE O.D.					

© 2021 TE Connectivity. All Rights Reserved.

DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	DWN E.CHEN 19OCT2022	MATERIAL 1	FINISH -
	CHK J.LI 19OCT2022		
	APVD Z.ZHOU 19OCT2022	NAME CABLE CLIP HVA HD400 MULTI CORE PLUG	
	PRODUCT SPEC 108-160599	SIZE A 4	CAGE CODE 00779
	APPLICATION SPEC 114-160337	DRAWING NO C=2392558	RESTRICTED TO -
	WEIGHT -	SCALE 1:1	
CUSTOMER DRAWING		SHEET 1 OF 1	REV A