


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISE	20APR2022	C.C	Z.Z
	C	ECN-24-269267	05JUN2024	T.L	Z.Z
	C1	ECN-24-297051	04DEC2024	T.L	Z.Z
	C2	PCN-25-240976	06MAY2025	S.T	Z.Z



-3 AS SHOWN

- 1 MATERIAL: PA66-GF, COLOR: SEE TABLE
2. BULK PACKAGED

C2

C2

16.7	17.3	Ø13.65	(0.83)	BLACK	INNER SPACER - 70mm ²	2395861-3	C
14.6	15.2	Ø11.45	(1.27)	NATURAL	INNER SPACER - 50mm ²	2395861-2	C
12.4	13	Ø9.65	(1.58)	ORANGE	INNER SPACER - 35mm ²	2395861-1	C
MIN.	MAX.						
CABLE O.D.		DIM.A	WEIGHT(g)	COLOR	CABLE SIZE	PART NO.	PART REV.

© 2021 TE Connectivity. All Rights Reserved.

DIMENSIONS:		DWN	26AUG2021	MATERIAL	1		FINISH
mm		P.LING	26AUG2021				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	26AUG2021				
±0.3		J.LI	26AUG2021				
0 PLC ±		APVD	26AUG2021				
1 PLC ±0.1		I.YIN					
2 PLC ±0.01		PRODUCT SPEC		NAME			
3 PLC ±0.001		108-160341		INNER_SPACER			
4 PLC ±0.0001		APPLICATION SPEC		HVP-HD1000			
ANGLES ±		114-160182/160411		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT		A 4	00779	C-2395861	-
CUSTOMER DRAWING				SCALE	2:1	SHEET	1 OF 1
						REV	C2