




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	INITIAL RELEASE	14FEB2022	SS	KPB
	A2	DRAWING UPDATED AS PER SUPPLIER DRAWING	13JUN2022	SS	KPB
	A3	PCN-23-187957	13JUN2024	SS	KPB




DETAIL A
SCALE 10:1




- NOTES
- 1 TE-SINGLE PART NUMBER.
 - 2 MATERIAL MARKING.
 - 3 CAVITY MARKING IF MULTIPLE CAVITY TOOL
 - 4 PARTING LINE
 - 5 REVISION MARKINGS (A=NO DOT, B=1 DOT, ETC) TO APPEAR IN THIS LOCATION.
 - 6 USE WIRE INSULATION O.D. RANGE OF 1.10mm TO 1.60mm.
 - 7 PART DIMENSIONS SHOWN ARE IN PART'S FREE STATE CONDITION.
 - 8 BULK PACKAGING IN PLASTIC BAG OR AS PER SPEC V2401251


SECTION A-A




AS SHOWN
9-2401251-1
FOR MISSING DIMENSIONS REFER 2401251-1



AS SHOWN 9-2401251-1
SCALE 3:1



AS SHOWN 2401251-1
SCALE 3:1



RUST RED	INHERENTLY LUBRICATED SILICONE SHORE HARDNESS 40±5	1.74	GROMMET SEAL	A	9-2401251-1
YELLOW	INHERENTLY LUBRICATED SILICONE SHORE HARDNESS 40±5	1.74	GROMMET SEAL	A	2401251-1
COLOR	MATERIAL	WEIGHT(g)	DESCRIPTION	REV	TE PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN SUPRIYA S IODEC2021		
DIMENSIONS: mm			CHK AMRUTHA C H IODEC2021		
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD KASHYAP P B IODEC2021		
0 PLC ±0.5			PRODUCT SPEC		
1 PLC ±0.13			APPLICATION SPEC		
2 PLC ±0.013			WEIGHT		
3 PLC ±0.0001			CUSTOMER DRAWING		
4 PLC ±0.0001			SCALE 5:1		
ANGLES ±			SHEET 1 OF 1		
FINISH			REV A3		
MATERIAL			RESTRICTED TO		



TE Connectivity

GROMMET SEAL, 11X0.35/0.5mm² WIRE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2401251	-
SCALE 5:1		SHEET 1 OF 1	REV A3