




REVISIONS					
変更					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	I	-	22DEC2022	-	-

RECOMMEND PC BOARD HOLE PATTERN: CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.57±0.1

24	Y	II	22.0	25.0	26.6	2-2429955-2
24	X	II	22.0	25.0	26.6	1-2429955-2
POS	KEY	n	A	B	C	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	28-Nov-23	TE TE Connectivity		
		CHK	Colin Chen			
		CHK	Rick Bian			
		APVD	Rick Bian			
DIMENSIONS: 単位: 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 名称		
		一般公差 ±0.3, ±5°		DYNAMIC D1100D 2.0mm PITCH		
		0-PLC ±		HDR ASSY (V-TYPE) PIP		
		1-PLC ±0.5		24POS		
		2-PLC ±0.13		SIZE		
		3-PLC ±0.013		CAGE CODE		
		4-PLC ±0.0001		DRAWING NO		
		ANGLES ±		114-5377		
MATERIAL 材料		FINISH 仕上		WEIGHT		
&material		-		-		
-		-		CUSTOMER DRAWING		
				SCALE 尺度		
				2:1		
				SHEET 1 OF 2		
				REV A		

4

3




2

1


© 2022BY -

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



24POS(X-KEY):1-2429955-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Colin Chen 28-Nov-23	 TE Connectivity					
		CHK Rick Bian 28-Nov-23						
		APVD Rick Bian 28-Nov-23	NAME DYNAMIC D1100D 2.0mm PITCH HDR ASSY (V-TYPE) PIP 24POS					
DIMENSIONS: mm		PRODUCT SPEC 108-161124	SIZE A3			CAGE CODE 00779	DRAWING NO C-2429955	RESTRICTED TO -
		APPLICATION SPEC 114-5377						
MATERIAL Material		WEIGHT -						
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.5 2 PLC ± 0.13 3 PLC ± 0.013 4 PLC ± 0.0001 ANGLES ± -		FINISH - -	CUSTOMER DRAWING					
			SCALE 2:1		SHEET 2 OF 2		REV A	