


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	22JUL2024	AG	TG



CIRCUIT LIST:

TE P/N	CAVITY 1	CAVITY 2	L	WIRE TYPE	HSG P/N	TE PART REV.
2473335-1	PINK	VIOLET	4000 ⁺⁶⁰ ₀	0.35	1802365-1	A
2473335-2	PINK	VIOLET	2000 ⁺⁴⁰ ₀	0.35	1802365-1	
2473335-3	PINK	VIOLET	1000 ⁺²⁰ ₀	0.35	1802365-1	

CODING W PINK	
CODING X PURPLE	
CODING Y GREY	

"D" PART

NOTES:

1. 100% ELECTRICAL TEST: ACCORDING TO TEST SPECIFICATION 108-18857
2. CRIMP TERMINALS PER TE SPEC 114-15132
3. PRINT TRACKING INFORMATION ON THE PRODUCT

A/R	A/R	A/R	MM	SEE TABLE	TWISTED WIRE,FLRY-A, BARE	2
1	1	1	PC	1802365-1	SQUIB ASSY 90 DEGREES CODE W PINK,FOR 0.35SQMM	1
-3	-2	-1	U/M	PART NO	DESCRIPTION	ITEM NO

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN A.GU 28AUG2023	TE Connectivity		
				CHK L.SHA 28AUG2023			
				APVD T.GUO 28AUG2023	NAME		
				PRODUCT SPEC	SQUIBLOK 90D CABLE ASSY		
				APPLICATION SPEC			
				WEIGHT 0	SIZE A2	CAGE CODE 00779	DRAWING NO C-2473335
				CUSTOMER DRAWING	SCALE 1:1	SHEET 1 of 1	REV A