






SRC2 84+0 MAIN HOUSING GREEN




- NOTES:
- MATERIALS:  
HOUSINGS: POLYESTER (PBT), GLASS FILLED, UL 94 HB  
SEAL: SILICONE RUBBER
  - VARIATION OF SHADE WITHIN OR BETWEEN BATCHES, OR DISCOLORATION IS ACCEPTABLE
  - MX150 BLADE TERMINALS TO BE USED WITH THESE ASSEMBLIES IN ALL CAVITIES, CRIMPED WITH CABLE INSULATION OUTER DIAMETER IN THE RANGE 1.5mm TO 2.7mm
  - PACKAGING SPECIFICATION: TEC-107-160003-02
  - THIS SHEET: 2500027-1 (OLD PN 938508400) (84+0) OPTION MATES WITH SRC2 PIN RECEPTACLE HOUSING ASSEMBLY (GREEN) PN 2500008-1 (OLD PN 932870001)
  - FLANGE GASKET OPTION: REFER TO 2500032-1
  - SUGGESTED DIMENSIONS FOR FLAT PLATE. CUSTOMER SHOULD VERIFY FIT IN THEIR OWN APPLICATION. ALL DIMENSIONS SYMMETRIC ABOUT CENTERLINES.
  - CLEARANCE FOR M4 COUNTERSUNK HEADS RECOMMENDED IN THESE HOLES.
  - PRESENCE OF TE LOGO OPTIONAL ON REAR COVER, FRONT COVER & HOUSING.





ACCEPTABLE CABLE INSULATION Ø RANGES (mm) - NOTE 3						
CAVITY SET						
G	F	E	D	C	B	A
1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7	1.5 - 2.7

4	MALE BACK SEAL	1	RUSTED RED
3	MALE REAR COVER	1	BLACK
2	MALE FRONT COVER(TPA)	1	GREEN
1	MALE HOUSING	1	GREEN
No.	DESCRIPTION	QTY.	COLOR
BILL OF MATERIAL			



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A3		ECO-20-009048	15JUL2020	MHS	MT
B		PCN-21-123224	23DEC2021	DRK	AW



938508400	2500027-1
OLD P/N	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MANOHAR H S 15JUL2020	TE Connectivity			
DIMENSIONS:		CHK M TRULL 15JUL2020				
mm		APVD M TRULL 15JUL2020	NAME SRC 84 PIN MALE BLADE HSG ASSY GREEN			
		PRODUCT SPEC TEC-108-160018	SIZE A2			
		APPLICATION SPEC TEC-114-160015				
MATERIAL -		WEIGHT -	CAGE CODE 00779		DRAWING NO C-2500027	RESTRICTED TO -
FINISH -		CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1	REV B