





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECO-20-009048	03AUG2020	TP	MT

- NOTES:
1. MATERIAL:POLYBUTYLENE TEREPHTHALATE (PBT), COLOUR: NATURAL
 2. UL FLAMMABILITY RATING: UL 94 V0
 3. PART DESIGNED TO BE USED IN SRC MALE POWER BLADE AND FEMALE RECEPTACLE ASSEMBLIES
 4. CAVITY NUMBER IN THIS LOCATION 2mm HIGH, RAISED 0.1mm MAX
 5. APPLICATION SPECIFICATION: TEC-114-160015
 6. MOQ 4000 PIECES. PARTS TO BE BULK PACKED IN BAGS OF 1000 PIECES WITH 4 BAGS IN A BOX
 7. THIS SHEET: 2500033-1 (OLD PN 937320001)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	T PRATIK	03AUG2020	 TE Connectivity	
		CHK	M TRULL	03AUG2020		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	M TRULL	03AUG2020	NAME	
		PRODUCT SPEC			SRC POWER BLIND CAVITY PLUG	
	0 PLC ±0.5 1 PLC ±0.5 2 PLC ±0.3 3 PLC ±0.3 4 PLC ±0.3 ANGLES ±0.5	APPLICATION SPEC			SIZE	CAGE CODE
		WEIGHT			A3	00779
MATERIAL	FINISH	CUSTOMER DRAWING			DRAWING NO	RESTRICTED TO
-	-	SCALE 5:1			SHEET 1 OF 1	REV A1