


CODICE FORNITORE "A 042"
(SUPPLIER CODE "A 047")

DATARIO
(DATE CODE)




LOGO "AMP"
("AMP" TRADE MARK)

PER DETTAGLIO POLARIZZAZIONI VEDERE FOGLIO 2 DI 3
PER P/NS CONTROPARTI PORTAMASCHI, VEDERE TABELLA.
(FOR POLARIZATION DETAIL SEE SHEET 2 OF 3, FOR
COUNTERPART CAP HSG. P/NS SEE THE TABLE).


(B1) CAVITA' ADATTA PER CONTATTI:
(TYP. CAVITY FOR CONTACTS:)

282374-1 SEZ. 0.3-0.5 mm² (FIAT No. 1-23197-44)
282375-1 SEZ. 0.75-1.5 mm² (FIAT No. 1-24834-44)

NO. DI IMPRONTA STAMPO
(MOULD CAVITY IDENTIF. NO.)



SEZIONE A-A
(SECTION A-A)



NUM. DI CAVITA'
(CIRCUIT IDENTIF. NO.)

1) PER RAPPRESENTAZIONE DIMA CONTROPARTE VEDERE FOGLIO 3 DI 3.
(FOR COUNTERPART DETAIL SEE SHEET 3 OF 3).

(B1) 2 QUOTA VALIDA SOLO PER VERSIONE 282441-1.
(VALID DIMENSION ONLY FOR 282441-1 VERSION)

OBSOLETE	282442-4	GRIGIO (GREY)	PBT (PBT UNFILLED)	282441-4
OBSOLETE	282442-3	BLU (BLUE)		282441-3
OBSOLETE	282442-2	NERO (BLACK)		282441-2
	282442-1	BIANCO (NATURAL)		282441-1
PORTAMASCHI VOLANTE (CAP HOUSING)		COLORE (COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)



CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO	
THIS DRAWING IS UNPUBLISHED.		RELEASE FOR PUBLICATION	
© COPYRIGHT IS BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING.		TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)	
B4	REVISED PER ECN-25-305243	AP/VN	07FEB 2026
B3	REVISED PER ECN-22-144343	AP/VN	18MAR 2022
B2	REVISED PER ECO-20-003218	AP/VN	08MAY 2020
B1	REVISED	M.G.	05
B	RELEASED AND REVISED FOR ET00-0298-97	M.P.	29-7 '97
2	AGG. CODICE FIAT	R.M.	25-10 '93
1	AGGIORNATO	R.M.	1-4 '93
REV.	REVISIONI (REVISION RECORD)	DIS.	DATA (DATE)
DESCRIPTION (DESCRIPTION) 070 SERIES MULTILOCK* CONN. PLUG HOUSING 6 POSITION (PORTAFEMMINE) DOUBLE ROW		LOC. SIZE NUMERO (LOC. SIZE)	
I A3		C-282441	
REV. B4		FOGLIO (SHEET) 1 DI 3	

RAPPRESENTAZIONE GRAFICA VERSIONI POLARIZZATE
(DETAIL REPRESENTATION OF POLARIZATION VERSIONS)


SCALA NON IPERDATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN)

METRIC


PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)



P/N 282366-2 NERO
(BLACK)



P/N 282366-3 BLU
(BLUE)






P/N 282366-4 GRIGIO
(GREY)

ASSE CAVITA'
(CAVITY AXIS)

ASSE CAVITA'
(CAVITY AXIS)


ASSE CAVITA'
(CAVITY AXIS)



1 QUOTA VALIDA PER VERSIONI 282441-2; -3; -4
(VALID DIMENSION ONLY FOR 282441-2; -3; -4 VERSIONS)

COLORE (COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)
CUSTOMER DWG. FOR REFERENCE ONLY	DISEGNO PER CLIENTE SOLO PER RIFERIMENTO	
THIS DRAWING IS UNPUBLISHED. RELEASE FOR PUBLICATION 19		
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING		
TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)	DIAM. ISOLANTE (INS. DIA. RANGE)	RANGO FILO (WIRE RANGE)
± 0.3		SCALA (SCALE)
ANGOLI (ANGLES)		2:1
DIS. (OR.)	DESCRIZIONE (DESCRIPTION) 070 SERIES MULTILOCK*	
CNT. (CHK)	CONN. PLUG HOUSING 6 POSITION (PORTAFEMMINA) DOUBLE ROW	
REV.	LOC. SIZE (LONG. HO)	REV.
REVISIONI (REVISION RECORD)	I A3 C-282441	B4
DIS. DATA (OR)		FOGLIO (SHEET)
APP. (APP.)		2 DI (COP.)
		3

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)



CONIARE LE BAVE DI TRANCIATURA
(NO TRIMMING BURRS ADMITTABLE)

2) TAB: OTTONE TEMPRA 4, STAGNATO
(TAB: BRASS TEMPER 4, TIN PLATED)

COLORE (COLOUR)		MATERIALE (MATERIAL)		NUMERO (PART NUMBER)	
CUSTOMER DWG. FOR REFERENCE ONLY			DISEGNO PER CLIENTE SOLO PER RIFERIMENTO		
-THIS DRAWING IS UNPUBLISHED-			RELEASE FOR PUBLICATION		19
© COPYRIGHT 19... BY ARP INCORPORATED, HARRISBURG, PA., ALL INTERNATIONAL RIGHT RESERVED, AND PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING.					
TOLLERANZE; SE NON DIVERSAMENTE SPECIFICATO		DIAM. ISOLANTE (INS. DIA. RANGE)		RANGO FILO (WIRE RANGE)	SCALA (SCALE)
TOLLERANZE; UNLESS OTHERWISE SPECIFIED					2:1
0 DEC. PLACE ±0.3 1 DEC. PLACE ±0.1 2 DEC. PLACE ±0.05					
ANGOL. (ANGLES) 0° 30'				TE Connectivity	
DIS. (CON.)		DESCRIPTION 070 SERIES MULTILOCK* (DESCRIPTION) CONN. PLUG HOUSING 5 POSITION (DIM A DI MONTAGGIO)			
CONT. (CHK)		LOC. SIG. NUMERO (C.G. NO.)		REV.	
APP. (SHEET 1 OF 3)		I A3 C-282441		B4	
TAP				FOGLIO (SHEET) 3 OF 3	