


CODICE FORNITORE "A 047"
(SUPPLIER CODE "A 047")


DATARIO
(DATE CODE)



LOGO "AMP"
("AMP" TRADE MARK)

CAVITA' ADATTE PER CONTATTI P/N:
(CAVITIES SUITABLE FOR CONTACTS P/N:)
282377-1 SEZ. 0.3-0.5 mm² (COD. FIAT 1/24833/44)
282378-1 SEZ. 0.75-1.5 mm² (COD. FIAT 1/24832/44)

NO. IMPRONTA STAMPO
(MOULD CAVITY IDENTIF. NO.)



SEZIONE A-A
(SECTION A-A)

NUM. DI CAVITA'
(CIRCUIT IDENTIF. NO.)

QUOTA VALIDA PER VERSIONE 282370-1
(VALID DIMENSION ONLY FOR P/N 282370-1)

PROFILO ALTERNATIVO
(ALTERNATIVE PROFILE)

3) PER DETTAGLIO POLARIZZAZIONI VEDERE FOGLIO 2 DI 2
PER P/NS CONTROPARTI PORTAFEMMINA, VEDERE TABELLA
(FOR POLARIZATION DETAILS SEE SHEET 2 OF 2
FOR COUNTERPART PLUG HSG. P/NS SEE THE TABLE).

OBSOLETE

282441-4	GRIGIO (GREY)	PBT (PBT UNFILLED)	282442-4
282441-3	BLU (BLUE)		282442-3
282441-2	NERO (BLACK)		282442-2
282441-1	BIANCO (NATURAL)		282442-1
PORTAFEMMINA VOLANTE (PLUG HOUSING)	COLORE (COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)

CUSTOMER DWG.
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED. RELEASE FOR PUBLICATION 19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT
RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING
TOLLERANZE, SE NON
DIVERSAMENTE SPECIFICATO
(TOLERANCES, UNLESS
OTHERWISE SPECIFIED)
DIAM. ISOLANTE
(INS. DIA. RANGED)
RANGO FILO
(WIRE RANGED)
SCALA
(SCALE)
2:1


B2	ECN-25-304763	AP	05 JAN 2025	± 0.3
B1	REVISED PER ECR-13-004824	M.G.	26 MAR 2013	± 2°
B	RELEASED AND REVISED FOR ET00-0298-97	M.P.	29-07-97	DIS. M. PALMA (DR.) 23 MAY '97
2	AGG. CODICE FIAT	R.M.	26-10-93	CONT. C. TARTARI (CHC.) 23 MAY '97
1	AGGIORNATO	R.M.	1-4-93	APP. APP.
REV.	REVISIONI (REVISION RECORD)	DIS. DATA (DR) (DATE)		
		LOC. SIZE	NUMERO (DWG NO)	REV. FOGLIO (SHEET)
		I A3	C-282442	B2 1 DI 2

TE Connectivity


DESCRIZIONE
(DESCRIPTION) 070 SERIES MULTILOCK*
CONN. CAP HOUSING 6 POSITION
(PORTAMASCHI) DOUBLE ROW

RAPPRESENTAZIONE GRAFICA VERSIONI POLARIZZATE
(DETAIL REPRESENTATION OF POLARIZATION VERSIONS)


SEZIONE PARZIALE M-M
(PARTIAL SECTION M-M)



P/N 282442-2 (NERO)
(BLACK)



P/N 282442-3 (BLU)
(BLUE)



P/N 282442-4 (GRIGIO)
(GREY)

QUOTA VALIDA PER VERSIONI 282442-2, 3, 4
(VALID DIMENSION ONLY FOR 282442-2, 3, 4 VERSION)

CUSTOMER DWG.
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED. RELEASE FOR PUBLICATION 19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT
RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING
TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)
DIA. ISOLANTE (INS. DIA. RANGE) RANGO FILO (WIRE RANGE) SCALA (SCALE)
± 0.3 2:1

TE Connectivity

DESCRIZIONE (DESCRIPTION) 070 SERIES MULTILOCK*
CONN. CAP HOUSING 6 POSITION
(PORTAMASCHI) DOUBLE ROW

LOC. SIZE NUMERO (DWG NO) REV. FOGLIO (SHEET)
I A3 C-282442 B2 2 OF 2

REV. REVISIONI (REVISION RECORD) DIS. DATA (CR) DATE

APP. (APP.)

DISTRIBUZIONE
(PRINT DIST.)