





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FIRST RELEASED	15AUG2017	WH	DZ




- 1 WIRE SIZE: 1.31mm² (16 AWG).
- 2 INSULATION RANGE: DIA 1.80–3.10 mm [.071–.122 in]
- 3 FINISHED: 2.54µm MIN PRE-TIN ALL OVER, WITH 0.762µm MIN NICKEL UNDER-PLATING ALL OVER
- 4 MATING PART: 2825206–1 (STRIP TYPE) OR 2825208–1 (LOOSE TYPE)



SECTION A–A



SECTION B–B



SECTION C–C

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN WARREN HUO 15AUG2017		 TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK DANIEL ZHANG 15AUG2017			
		APVD DANIEL ZHANG 15AUG2017		NAME TERMINAL, SOCKET VAL-U-LOK(TM) HCS	
		PRODUCT SPEC 108-150000			
		APPLICATION SPEC 114-13172			
		WEIGHT 0			
TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 0.25 [.010] 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± ± ANGLES ±		FINISH		SIZE A2	
MATERIAL SEE TABLE		SEE TABLE		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-2825207	
				RESTRICTED TO —	
				SCALE N/A	
				SHEET 1 of 1	
				REV A	