


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A1		ECR-16-007102	17MAY2016	GSK	AP

- NOTES:
- EACH ITEM AND ASSEMBLY MUST COMPLY WITH EUROPEAN REDUCTION OF HAZARDOUS SUBSTANCES (RoHS) REGULATION. UNDER DIRECTIVE 2011/65/EU AND HARMONIZED STANDARD EN 50581:2012.
 - DO NOT SOLDER CONTACT, CRIMP ONLY
 - IDENTIFY POSITION PE, LOADING POSITIONER PE TO SOCKET PE
 - PE CONTACT CIRCUIT IDENTIFIED BY EXTENDED LENGTH POLARIZED "KEY"
 - ELECTRICAL TEST:
 100% OPEN SHORT&MISS WIRE TEST
 CONTACT RESISTANCE: 2 OHM MAX

TE PN
 2829492-1



CONNECTOR1

WIRE DIAGRAM

CONNECTOR 1	WIRE COLOR
L1	BROWN
N	BLUE
L3	
S2	GRAY
S1	BLACK
L2	
PE	GREEN/YELLOW

QTY	UoM	DESCRIPTION	ITEM
5	PC	14 AWG Socket Contacts	6
1	PC	Socket Housing Assembly 5 POS. A CODING	5
AR	M	Cable, H07RN-F, 14/5 Black, 13.3-17.0mm OD (Mueller 4101405)	6
1	PC	Cable Ring Nut 11-14mm OD	3
1	PC	Cable Clamp/Seal Assembly 11-14mm OD	2
1	PC	Contact/Positioner Assembly	1
-1	UoM	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.BURZYŃSKI 25MAY2015	TE Connectivity	
DIMENSIONS: mm		CHK A.V.ZANDVOORT 25MAY2015		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A.V.ZANDVOORT 25MAY2015	NAME SEALED 567 POS SOCKET STD HARMONIZED CABLE	
0 PLC ± 0,5 1 PLC ± 0,5 2 PLC ± 0,5 3 PLC ± - 4 PLC ± - ANGLES ± 2°		PRODUCT SPEC -	-	
MATERIAL -		FINISH -	APPLICATION SPEC -	RESTRICTED TO -
		WEIGHT	SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C-2829492	SCALE NTS
			SHEET 1 OF 1	REV A1