

RECOMMENDED PCB PATTERN




ALL CONTACTS



1-2842106-0 AS SHOWN

PICK AND PLACE CAP	3
CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANKIT YADAV	08AUG2019
DIMENSIONS:		CHK KARTHIK JK	13AUG2019
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD PRASHANTH S	14AUG2019
mm	0 PLC $\pm$ 2 PLC ± 0.2 2 PLC ± 0.15 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm 2^\circ$	PRODUCT SPEC	108-64040
		APPLICATION SPEC	114-32259
MATERIAL	FINISH	WEIGHT	-
SEE NOTES	SEE NOTES	CUSTOMER DRAWING	

		TE Connectivity	
NAME AMPMODU 2mm BREAKAWAY HEADER, SINGLE ROW, VERTICAL SMD, 0.1 Au. TUBE			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	Ⓒ=2842106	-
		SCALE	REV
		5:1	B
		SHEET	OF
		1	1

48.0	50.0	25	2-2842106-5
46.0	48.0	24	2-2842106-4
44.0	46.0	23	2-2842106-3
42.0	44.0	22	2-2842106-2
40.0	42.0	21	2-2842106-1
38.0	40.0	20	2-2842106-0
36.0	38.0	19	1-2842106-9
34.0	36.0	18	1-2842106-8
32.0	34.0	17	1-2842106-7
30.0	32.0	16	1-2842106-6
28.0	30.0	15	1-2842106-5
26.0	28.0	14	1-2842106-4
24.0	26.0	13	1-2842106-3
22.0	24.0	12	1-2842106-2
20.0	22.0	11	1-2842106-1
18.0	20.0	10	1-2842106-0
16.0	18.0	9	2842106-9
14.0	16.0	8	2842106-8
12.0	14.0	7	2842106-7
10.0	12.0	6	2842106-6
8.0	10.0	5	2842106-5
6.0	8.0	4	2842106-4
DIM "F"	DIM "E"	POS	TE PN