



[illegible]

ALL CONTACTS



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANKIT YADAV	08AUG2019
DIMENSIONS: mm		CHK KARTHIK JK	13AUG2019
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD PRASHANTH S	14AUG2019
	0 PLC ±- 1 PLC ±0.2 2 PLC ±0.15 3 PLC ±- 4 PLC ±- ANGLES ±2°	PRODUCT SPEC 108-64040	
	MATERIAL SEE NOTES	FINISH SEE NOTES	APPLICATION SPEC 114-32259
		WEIGHT	-
		CUSTOMER DRAWING	

		TE Connectivity	
NAME AMPMODU 2mm BREAKAWAY HEADER, SINGLE ROW, VERTICAL SMD, 0.76 Au, TUBE			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C=2842108	-
		SCALE 5:1	SHEET 1 OF 1 REV B

48.0	50.0	25	2-2842108-5
46.0	48.0	24	2-2842108-4
44.0	46.0	23	2-2842108-3
42.0	44.0	22	2-2842108-2
40.0	42.0	21	2-2842108-1
38.0	40.0	20	2-2842108-0
36.0	38.0	19	1-2842108-9
34.0	36.0	18	1-2842108-8
32.0	34.0	17	1-2842108-7
30.0	32.0	16	1-2842108-6
28.0	30.0	15	1-2842108-5
26.0	28.0	14	1-2842108-4
24.0	26.0	13	1-2842108-3
22.0	24.0	12	1-2842108-2
20.0	22.0	11	1-2842108-1
18.0	20.0	10	1-2842108-0
16.0	18.0	9	2842108-9
14.0	16.0	8	2842108-8
12.0	14.0	7	2842108-7
10.0	12.0	6	2842108-6
8.0	10.0	5	2842108-5
6.0	8.0	4	2842108-4
DIM "F"	DIM "E"	POS	TE PN