





REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	30AUG2019	SS	PS
	A1	REMOVED TOLERANCE FROM DIM F	18DEC 2019	AY	PS
	A2	PARTS OBSOLESCENCE	22JUN2023	BGC	PS




NOTES:


1. MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0;COLOR- BLACK
CONTACT PIN : COPPER ALLOY
FINISH : MIN 2.0 μm BRIGHT TIN OVER MIN NICKEL UNDER PLATING.
2. PACKAGING: BULK PACK.
-  3. TOLERANCE NOT CUMULATIVE.
4. CUTTING BURR MAX. 0.25 mm.



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW /PIN-IN-PASTE




OBSOLETE

48.0	50.0	25	2-2842137-5
46.0	48.0	24	2-2842137-4
44.0	46.0	23	2-2842137-3
42.0	44.0	22	2-2842137-2
40.0	42.0	21	2-2842137-1
38.0	40.0	20	2-2842137-0
36.0	38.0	19	1-2842137-9
34.0	36.0	18	1-2842137-8
32.0	34.0	17	1-2842137-7
30.0	32.0	16	1-2842137-6
28.0	30.0	15	1-2842137-5
26.0	28.0	14	1-2842137-4
24.0	26.0	13	1-2842137-3
22.0	24.0	12	1-2842137-2
20.0	22.0	11	1-2842137-1
18.0	20.0	10	1-2842137-0
16.0	18.0	9	2842137-9
14.0	16.0	8	2842137-8
12.0	14.0	7	2842137-7
10.0	12.0	6	2842137-6
8.0	10.0	5	2842137-5
6.0	8.0	4	2842137-4
4.0	6.0	3	2842137-3
2.0	4.0	2	2842137-2

1-2842137-0 AS SHOWN

CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUBHASREE S		06AUG2019		 TE Connectivity									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK KARTHIK JK		08AUG2019		NAME AMPMODU 2mm BREAKAWAY HEADER, DUAL ROW, VERTICAL, Sn, BULK							
		0 PLC ± 1 PLC ±0.2 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ±2°		APVD PRASHANTH S		09AUG2019									
				PRODUCT SPEC 108-64040											
				APPLICATION SPEC 114-32259											
MATERIAL SEE NOTES		FINISH SEE NOTES		WEIGHT -		SIZE A3		CAGE CODE 00779		DRAWING NO C-2842137		RESTRICTED TO -			
CUSTOMER DRAWING										SCALE 5:1		SHEET 1 OF 1		REV A2	