



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	30AUG2019	SS	PS
	A1	REMOVED TOLERANCE FROM DIM F	18DEC2019	AY	PS
	A2	PARTS OBSOLESCENCE	23JUN2023	BGC	PS

NOTES:

1. MATERIAL
HOUSING & P&P CAP : HIGH TEMPERATURE THERMOPLASTIC,
UL94-V0;COLOR- BLACK
CONTACT PIN : COPPER ALLOY
FINISH :
MATING SIDE : MIN. 0.1 µm GOLD OVER NICKEL UNDER PLATING.
SOLDER SIDE : MIN. 2.0 µm BRIGHT TIN OVER NICKEL UNDER PLATING.
2. PACKAGING: TUBE (WITH PICK AND PLACE CAP).
3. TOLERANCE NOT CUMULATIVE.
4. CUTTING BURR MAX. 0.25 mm





OBSOLETE	48.0	50.0	25	2-2842154-5
	46.0	48.0	24	2-2842154-4
	44.0	46.0	23	2-2842154-3
	42.0	44.0	22	2-2842154-2
	40.0	42.0	21	2-2842154-1
	38.0	40.0	20	2-2842154-0
	36.0	38.0	19	1-2842154-9
	34.0	36.0	18	1-2842154-8
	32.0	34.0	17	1-2842154-7
	30.0	32.0	16	1-2842154-6
	28.0	30.0	15	1-2842154-5
	26.0	28.0	14	1-2842154-4
	24.0	26.0	13	1-2842154-3
	22.0	24.0	12	1-2842154-2
	20.0	22.0	11	1-2842154-1
OBSOLETE	18.0	20.0	10	1-2842154-0
	16.0	18.0	9	2842154-9
	14.0	16.0	8	2842154-8
	12.0	14.0	7	2842154-7
	10.0	12.0	6	2842154-6
	8.0	10.0	5	2842154-5
	6.0	8.0	4	2842154-4
	DIM "F"	DIM "E"	POS. PER ROW	TE PN


1-2842154-0 AS SHOWN

PICK AND PLACE CAP	3
CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 07AUG2019 SUBHASREE S	TE Connectivity	
		CHK 13AUG2019 KARTHIK JK		
		APVD 14AUG2019 PRASHANTH S		
		PRODUCT SPEC 108-64040		
DIMENSIONS: mm		APPLICATION SPEC 114-32259	NAME AMPMODU 2mm BREAKAWAY HEADER, DUAL ROW, RIGHT ANGLE, 0.1 Au, TUBE, WITH PICK AND PLACE CAP	
		WEIGHT -	SIZE A3	CAGE CODE 00779
MATERIAL SEE NOTES		FINISH SEE NOTES	DRAWING NO C-2842154	RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 1
				REV A2



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW /PIN-IN-PASTE