






LOC	DIST	REVISIONS					
		REVISIONI					
1	-	P	LTR REV	DESCRIPTION DESCRIZIONE	DATE DATA	DWN DIS.	APVD APP.
			A	(FIRST ISSUE) PRIMA EMISSIONE ET00-0364-99	17NOV99	G.S.	A.G.
			A1	UPDATED DRAWING (ET00-0126-00)	09MAY00	M.S.	O.C.
			B	RELEASED FOR PRODUCTION ET00-0164-00	--JUN-00	M.S.	O.C.





NOTE:
(NOTES:)
MATERIALI: (MATERIALS)
1) SEDE ADATTE PER MODULO CRIMP 2.54 mm PITCH
P/N 284134 -1 E -2 VEDI TAB. FOGLIO 2/2
(SLOT SUITABLE FOR HOUSING CRIMP 2.54 mm PITCH
P/N 2841314-1 END -2 SEE TAB. SHEET 2/2)
2) SEDE ADATTA PER MODULO CRIMP 2.54 mm PITCH
P/N 284134-3 E -4 VEDI TAB. FOGLIO 2/2
(SLOT SUITABLE FOR HOUSING CRIMP 2.54 mm PITCH
P/N 2841314-3 END -4 SEE TAB. SHEET 2/2)
MATERIALI: (MATERIALS)
3) CORAZZA: PA6.6 CARICATO VETRO VEDI TAB. FOGLIO 2/2
PER COLORE.
(SHELL: PA 6.6 GLASS FILLED SEE TAB. SHEET 2/2 FOR COLOUR)
4) LEVA: PA 6.6 CARICATO VETRO COLORE ROSSO
(LEVER: PA 6.6 GLASS FILLED RED COLOUR)
4) IL PRODOTTO VIENE FORNITO CON LEVA IN POSIZIONE CHIUSA.
(THE FRAME IS SUPPLIED WITH LEVER IN CLOSED POSITION)

284360-1 COME MOSTRATO (AS SHOWN)


THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. QUESTO DISEGNO E' UN DOCUMENTO DI PROPRIETA' E RESPONSABILITA' DELL' AMP INCORPORATED. E' SOGGETTO A VARIAZIONI. PER OTTENERE L'ULTIMA REVISIONE DEL DISEGNO CONTATTARE L'UFFICIO TECNICO RESPONSABILE.		DWN/DIS. G. STELLA 17NOV99	AMP Italia S.p.A. C.so F.lli Cervi 15 Collegno (TO)	
DIMENSIONS: DIMENSIONI: mm		CHK/CONT. O. CANUTO 17NOV99	NAME NOME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO		APVD/APP. A. GENTA 17NOV99	FRAME 18 POSITION CRIMP/CRIMP 2.54 mm PITCH	
0 PLC/DEC ±0.3 1 PLC/DEC ±0.3 2 PLC/DEC ±0.3 3 PLC/DEC ± 4 PLC/DEC ± ANGLES/ANGOLI ±		PRODUCT SPEC SPEC DI PRODOTTO	SIZE A3	
MATERIAL MATERIALE		APPLICATION SPEC SPEC DI APPLICAZIONE	CAGE CODE 00779	DRAWING NO NUMERO C-284360
FINISH FINITURA		WEIGHT PESO	RESTRICTED TO	
3		CUSTOMER DRAWING		DESIGNO PER CLIENTE SOLO PER RIFERIMENTO
3		SCALE SCALA 2:1		SHEET FOGLIO 1 OF DI 2
		REV B		

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS							
© COPYRIGHT 19		BY AMP INCORPORATED. ALL RIGHTS RESERVED.		P		LTR		DESCRIPTION		DATE		DWN		APVD	
								VEDI FOGLIO 1/2 (SEE SHEET 1/2)							

P/N	RAPPRESENTAZIONE GRAFICA (GRAPHICAL REPRESENTATION)	COLORE (COLOUR)	CONNETTORE CRIMP (HOUSING CRIMP P/N	COLORE CONN. (HSG.COLOUR)	CONTROPARTE (COUNTERPART)
284360-1		NERO (BLACK)	284134-1	NERO (BLACK)	DIMA P/N 953466 (HEADER P/N 953466)
			284134-3	BLUE (BLUE)	
284360-2		GRIGIO (GRAY)	284134-2	GRIGIO (GRAY)	DIMA P/N 953466 (HEADER P/N 953466)
			284134-4	MARRONE (BROWN)	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±0.3

1 PLC ±0.1

2 PLC ±0.05

3 PLC ±

4 PLC ±

ANGLES ±

FINISH

DWN
G. STELLA 19NOV99

CHK
O. CANUTO 19NOV99

APVD
A. GENTA 19NOV99

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

AMP

AMP Italia S.p.A.
C.so F.lli Cervi 15 Collegno (TO)

NAME

FRAME 18 POSITION
CRIMP/CRIMP
2.54 mm PITCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=C284360

SCALE 2:1

SHEET 2 OF 2

REV B

AMP 1470-19 REV 27JUN96