




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
2		REVISED	29APR2006	SZ	SY
3		REVISED	08MAY2006	SZ	SY
4		REV PER ECR-06-024870	23OCT2006	SZ	SY
6		NOTE 1 DELETED	09OCT2024	VNB	RCG



- ⑥ ⚠ DELETED
- ② MATERIAL: THERMO PLASTIC, UL94 V-0.
- ③ DATUM LOCATIONS AND BASIC DIMENSIONS TO BE ESTABLISHED BY THE CUSTOMER.
- ④ BULKHEAD THICKNESS RANGE: .031 - .100.
- ⑤ CONNECTOR MATED TO PANEL FROM OPPOSITE SIDE.
- ⑥ NO BURRS ALLOWED ON OPPOSITE (MATING) SIDE.
- ⑦ CONNECTOR KEEP OUT ZONE.
- ⑧ MOUNT CONNECTOR WITH TYCO HARDWARE KIT (SEE TABLE) FOR .050 [1.27mm] MIN RADIAL FLOAT.



1600914-1	5ACP + 24S + 1RF + 5ACP	292491-2
1600914-1	5ACP + 24S + 1RF + 5ACP	292491-1
KIT P/N	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.ZHAO 09-Oct-24	TE Connectivity	
		CHK S.ZHAO 31MAR2006		
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S.YAO	NAME PANEL MOUNT CABLE WITH GUIDES MULTI-BEAM XL W/ COAX	
INCHES	0 PLC ±.01 1 PLC ±.01 2 PLC ±.01 3 PLC ±.005 4 PLC ±.002	PRODUCT SPEC 108-2157		
	ANGLES ±2°	APPLICATION SPEC 114-13112	SIZE CAGE CODE DRAWING NO. A100779C=292491	
MATERIAL	FINISH	WEIGHT		
-	-	-	CUSTOMER DRAWING	
		SCALE 1:1	SHEET 1 OF 2	REV 6

