






LOC		DIST		REVISIONS				
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		D9		ADD NEW DASH NUMBER -19	09AUG2012	ML	SZ	
		E1		ADD NEW DASH NUMBER 2-1	05JAN2015	CZ	SZ	
		E2		NOTE 2 DELETED	09OCT2024	VNB	RCG	



ISOMETRIC VIEW



- 1 MATERIAL: THERMO PLASTIC, UL94 V-0.
- E2 2 DELETED
- 3 PANEL THICKNESS = .040±.005
- 4 CONNECTOR KEEP OUT ZONE.
- 5 POWER CONTACT REFERENCE:
PART NUMBER: 1600960 & 1600961
MATERIAL: COPPER ALLOY
FINISH (INTERFACE):.0000030 Au OVER .0000050 Ni
- 6 DASH NUMBERS INDICATED ARE NOT RELEASED FOR PRODUCTION.
- 7 VARIABLE DIMENSION SHOW ON THE TABLE.



LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
rev_sym_1	1566	8H5E111		rev_delete_v_1	dwn_1	appr_1
rev_sym_2	rev_desc_2			rev_delete_v_2	dwn_2	appr_2
rev_sym_3	rev_desc_3			rev_delete_v_3	dwn_3	appr_3
rev_sym_4	rev_desc_4			rev_delete_v_4	dwn_4	appr_4

1.840	.300	1.200	1.550	.475	3ACP(12AWG)	2-292499-1
3.465		2.825	3.175	.525	6ACP(8AWG)	2-292499-0
1.840	.300	1.200	1.550	.475	3ACP(8AWG)	1-292499-9
2.365	.375	1.725	2.075	.475	4P(8AWG)	1-292499-8
2.040	.375	1.400	1.750	.500	3ACP(8AWG)	1-292499-6
2.190	.300	1.550	1.900	.500	4ACP(10AWG)	1-292499-5
1.940	.200	1.300	1.650	.425	5HDP(12AWG)	1-292499-4
3.465		2.825	3.175	.525	6ACP(10AWG)	1-292499-3
2.340	.200	1.700	2.050	.425	7HDP(12AWG)	1-292499-2
2.440	.300	1.800	2.150	.475	5ACP(8AWG)	1-292499-1
2.440	.250	1.800	2.150	.450	6P(12AWG)	292499-8
2.940	.250	2.300	2.650	.450	8P(12AWG)	292499-7
1.940	.250	1.300	1.650	.450	4P(12AWG)	292499-4
2.140	.300	1.500	1.850	.475	4ACP(12AWG)	292499-3
2.440	.300	1.800	2.150	.475	5ACP(12AWG)	292499-2
1.840	.300	1.200	1.550	.475	3ACP(12AWG)	292499-1
DIM R REF	DIM S	DIM U	DIM L	DIM K	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S.ZHAO

CHK
S.ZHAO

APVD
S.ZHAO

08AUG2006
08AUG2006
-

DIMENSIONS:
INCHES

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±*
±.01
±.005
±.002
±1*

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

PRODUCT SPEC
108-2157
APPLICATION SPEC
114-13112

WEIGHT
-

NAME
SLIDE TO LOCK PANEL MOUNT CABLE
RECEPTACLE HOUSING, WITH GUIDES,
MULTI-BEAM XL

SIZE
A1

CAGE CODE
00779

DRAWING NO
292499

RESTRICTED TO
-

Customer Drawing

SCALE
2:1






SHEET
2








OF
4







REV
E2







TE Connectivity

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
rev_sym_1566	8H6E111			rev_delete_v_dwn_1	lapp_r		1
rev_sym_2rev_desc_2				rev_delete_v_dwn_2	lapp_r		2
rev_sym_3rev_desc_3				rev_delete_v_dwn_3	lapp_r		3
rev_sym_4rev_desc_4				rev_delete_v_dwn_4	lapp_r		4








PART NUMBER	ROWS		POWER			
			P3	P2	P1	
292499-1	D C B A					
3ACP						




PART NUMBER	ROWS		POWER					
			P5	P4	P3	P2	P1	
292499-2	D							
	C							
	B							
	A							
5ACP								

PART NUMBER	ROWS		POWER				
			P4	P3	P2	P1	
292499-3	D						
	C						
	B						
	A						
4ACP							

PART NUMBER	ROWS		POWER				
			P 4	P 3	P 2	P 1	
292499-4	D						
	C						
	B						
	A						
4P							

PART NUMBER	ROWS		POWER								
			P8	P7	P6	P5	P4	P3	P2	P1	
292499-7	D										
	C										
	B										
	A										
8P											



PART NUMBER	ROWS		POWER						
			P6	P5	P4	P3	P2	P1	
292499-8	D								
	C								
	B								
	A								
6P									







RM	STANDARD POWER CONTACT
RA	MFBL POWER CONTACT
CODE	DESCRIPTION
CONTACT TABLE	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. ZHAO	08AUG2006	TE Connectivity	
		CHK S. ZHAO	08AUG2006		
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ±"		PRODUCT SPEC	
		1 PLC ±.01		108-2157	
		3 PLC ±.005		APPLICATION SPEC	
		4 PLC ±.002		114-13112	
MATERIAL		FINISH		WEIGHT	
-		-		-	
				Customer Drawing	
				SCALE 2:1	
				SHEET 3 OF 4	
				REV E2	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
		rev_sym_1566	080811		rev_delete_v_dwn_1	app_r	
		rev_sym_2	rev_desc_2		rev_delete_v_dwn_2	app_r	
		rev_sym_3	rev_desc_3		rev_delete_v_dwn_3	app_r	
		rev_sym_4	rev_desc_4		rev_delete_v_dwn_4	app_r	



PART NUMBER	ROWS		POWER					
			P5	P4	P3	P2	P1	
I-292499-1	D C B A		RM	RA	RM	RA	RM	
5ACP								


PART NUMBER	ROWS		POWER			
			P3	P2	P1	
I-292499-6	D C B A		RM	RM	RM	
3ACP						



PART NUMBER	ROWS		POWER							
			P7	P6	P5	P4	P3	P2	P1	
I-292499-2	D C B A		RM		RM		RM		RM	
7HDP										

PART NUMBER	ROWS		POWER				
			P4	P3	P2	P1	
I-292499-8	D C B A		RA	RM	RM	RM	
4P							



D7



PART NUMBER	ROWS		POWER						
			P6	P5	P4	P3	P2	P1	
I-292499-3	D C B A		RM	RM	RM	RM	RM	RM	
6ACP									



 .425
5PLC


PART NUMBER	ROWS		POWER					
			P5	P4	P3	P2	P1	
I-292499-4	D C B A		RM		RM		RM	
5HDP								



NO LOACING CONTACT

PART NUMBER	ROWS		POWER				
			P4	P3	P2	P1	
I-292499-5	D C B A		RA	RA	RM	RM	
4ACP							

PART NUMBER	ROWS		POWER			
			P3	P2	P1	
I-292499-9	D C B A		RM	RA	RM	
3ACP						

PART NUMBER	ROWS		POWER						
			P6	P5	P4	P3	P2	P1	
2-292499-0	D C B A		RM	RM	RM	RM	RM	RM	
6ACP									

 .425
5PLC

PART NUMBER	ROWS		POWER			
			P3	P2	P1	
2-292499-1	D C B A		RA	RM	RM	
3ACP						

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

S.ZHAO

08AUG2006


CHK

S.ZHAO

08AUG2006

DIMENSIONS:

INCHES



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

±"

1 PLC

±.01

2 PLC

±.01

3 PLC

±.005

4 PLC

±.002

ANGLES

±1°

FINISH

-

MATERIAL

-

Customer Drawing

DWN

S.ZHAO

08AUG2006

CHK

S.ZHAO

08AUG2006

APVD

S.ZHAO

-

PRODUCT SPEC

108-2157

APPLICATION SPEC

114-13112

WEIGHT

-

Customer Drawing

NAME

SLIDE TO LOCK PANEL MOUNT CABLE RECEPTACLE HOUSING, WITH GUIDES, MULTI-BEAM XL

SIZE

CAGE CODE

DRAWING NO

A100779

C=292499

RESTRICTED TO

-

SCALE

2:1

SHEET

4

OF

4

REV

E2