

LOC	DIST	REVISIONS						
ES	00	P	LTR	DESCRIPTION		DATE	DWN	APVD

NOTES:
ELECTRICAL

NOMINAL IMPEDANCE(D_hm): 50
FREQUENCY RANGE: 0-3 G
VSWR: 1.35 MAX
CONTACT RESISTANCE:
-CETER CONTACT 5 MILLIDHM MAX
-OUTER CONTACT 2.5 MILLIDHM MAX
INITIAL INSULATION RESISTANCE(MEGDHMS):
-1000 MIN
DIELECTRIC WITHSTANDING VOLTAGE(VAC)
-500V rms


MECHANICAL

INTERFACE DIMENSIONS:MIL-STD-348A
IEC169-19
DURABILITY: 500 TIMES MIN

ENVIRONMENTAL

TEMPERATURE RANGE, OPERATING:
-55°C TD +155°C

COMPENENT	MATERIAL	FINISH
SHELL	BRASS	GOLD PLATING
DIELECTRIC	PTFE	N/A
CENTER CONTACT	BRASS	GOLD



THIS DRAWING IS A CONTROLLED DOCUMENT.										TYCO PART NO. 292855-1	
DWN		MICK NI		09FEB06		tyco Electronics				Tyco Electronics Corporation	
CHK		James Qu		09FEB06		shanghai cn					
APVD		James Qu		09FEB06		NAME		SSMB JACK FOR PCB			
PRODUCT SPEC		—									
APPLICATION SPEC		—									
WEIGHT		—									
CUSTOMER DRAWING		A3		00779		G=292855					
SCALE		6:1		SHEET		1		OF		1	
REV		C									